

# D-Sub Crimp Male Connector

**multicomp** PRO


**RoHS  
Compliant**



## Specifications

Current Rating	: 3 Amp
Insulation Resistance	: 5000M min. at 500V DC {for 1 minute}
Dielectric withstands Voltage	: AC 1000V min.
Operating Temperature	: -25°C to +85°C
Contact Type	: Plug
Contact Resistance	: 15mΩ max. mated
Insulation Material	: PBT & Glass-fiber reinforced UL-94V-0
Number of Positions	: 9
Colour Code	: Black
Metal Shell Finish	: The front shell and back shell, both Tin plated, without grounding indents on the front shell
Mounting Type	: Standard Hole

## Diagram



## Part Number Table

Description	Part Number
D-Sub Crimp Male Connector, 9 Contacts, Cable Mount	MC24555

Dimensions : Inches (Millimetres)

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO