


Hexagon Socket Head Screw multicomp^{PRO}

RoHS
Compliant



Polyether



Polyvinylidene

Features

- The rubber mouth of the screw length (L) is less than or equal to 5%.
- If screw is used with a nut, we recommend using the screw and nut made of the same material.
- The values in the table is only for reference , not a guarantee value.
- Please use a torque wrench to tighten. The recommended tightening torque is 50% of the breaking torque

Polyether


Description

PEEK (Polyether ether ketone) is a semi crystalline special engineering plastic with ultra-high performance; Strong chemical resistance, concentrated sulfuric acid is the only universal chemical that can dissolve PEEK. It has excellent heat resistance, wear resistance, flame retardancy, and hydrolysis resistance.

Applications

- Electronic and electrical appliances
- Photovoltaic and semiconductor industries
- Military industry
- Medical devices
- Aerospace and other fields

Diagram



Hexagon Socket Head Screw **multicomp**PRO

Part Number Table

Description	M	DK	K	S	Part Number
Hexagon Socket Head Screw, PEEK	M3 × 6	5.5	2.93	2.55	MP014133
	M3 × 8	5.5	2.93	2.55	MP014134
	M3 × 10	5.5	2.93	2.55	MP014135
	M3 × 12	5.5	2.93	2.55	MP014136
	M3 × 16	5.5	2.93	2.55	MP014137
	M3 × 20	5.5	2.93	2.55	MP014138
	M3 × 25	5.5	2.93	2.55	MP014139
	M4 × 6	7	3.91	3.05	MP014140
	M4 × 8	7	3.91	3.05	MP014141
	M4 × 10	7	3.91	3.05	MP014142
	M4 × 12	7	3.91	3.05	MP014143
	M4 × 16	7	3.91	3.05	MP014144
	M4 × 20	7	3.91	3.05	MP014145
	M4 × 25	7	3.91	3.05	MP014146
	M4 × 30	7	3.91	3.05	MP014147
	M5 × 8	8.5	4.91	4.06	MP014148
	M5 × 10	8.5	4.91	4.06	MP014149
	M5 × 12	8.5	4.91	4.06	MP014150
	M5 × 16	8.5	4.91	4.06	MP014151
	M5 × 20	8.5	4.91	4.06	MP014152
	M5 × 25	8.5	4.91	4.06	MP014153
	M5 × 30	8.5	4.91	4.06	MP014154
	M5 × 35	8.5	4.91	4.06	MP014155
	M6 × 8	10	5.85	5.08	MP014156
	M6 × 10	10	5.85	5.08	MP014157
	M6 × 12	10	5.85	5.08	MP014158
	M6 × 16	10	5.85	5.08	MP014159
	M6 × 20	10	5.85	5.08	MP014160
	M6 × 25	10	5.85	5.08	MP014161
	M6 × 30	10	5.85	5.08	MP014162
	M6 × 35	10	5.85	5.08	MP014163
	M6 × 40	10	5.85	5.08	MP014164
	M6 × 45	10	5.85	5.08	MP014165
	M6 × 60	10	5.85	5.08	MP014166
	M6 × 65	10	5.85	5.08	MP014167
	M8 × 10	13	7.82	6.08	MP014168
	M8 × 12	13	7.82	6.08	MP014169
	M8 × 16	13	7.82	6.08	MP014170

Hexagon Socket Head Screw **multicomp**PRO

Description	M	DK	K	S	Part Number
Hexagon Socket Head Screw, PEEK	M8 × 20	13	7.82	6.08	MP014171
	M8 × 30	13	7.82	6.08	MP014172
	M8 × 35	13	7.82	6.08	MP014173
	M8 × 40	13	7.82	6.08	MP014174
	M8 × 45	13	7.82	6.08	MP014175
	M8 × 65	13	7.82	6.08	MP014176
Hexagon Socket Head Screw, PVDF	M3 × 6	5.5	2.93	2.55	MP014385
	M3 × 8	5.5	2.93	2.55	MP014386
	M3 × 10	5.5	2.93	2.55	MP014387
	M3 × 12	5.5	2.93	2.55	MP014388
	M3 × 16	5.5	2.93	2.55	MP014389
	M3 × 20	5.5	2.93	2.55	MP014390
	M3 × 25	5.5	2.93	2.55	MP014391
	M4 × 6	7	3.91	3.05	MP014392
	M4 × 8	7	3.91	3.05	MP014393
	M4 × 10	7	3.91	3.05	MP014394
	M4 × 12	7	3.91	3.05	MP014395
	M4 × 16	7	3.91	3.05	MP014396
	M4 × 20	7	3.91	3.05	MP014397
	M4 × 25	7	3.91	3.05	MP014398
	M4 × 30	7	3.91	3.05	MP014399
	M5 × 6	8.5	4.91	4.06	MP014400
	M5 × 8	8.5	4.91	4.06	MP014401
	M5 × 10	8.5	4.91	4.06	MP014402
	M5 × 12	8.5	4.91	4.06	MP014403
	M5 × 16	8.5	4.91	4.06	MP014404
	M5 × 20	8.5	4.91	4.06	MP014405
	M5 × 25	8.5	4.91	4.06	MP014406
	M5 × 30	8.5	4.91	4.06	MP014407
	M5 × 35	8.5	4.91	4.06	MP014408
	M5 × 40	8.5	4.91	4.06	MP014409
	M6 × 6	10	5.85	5.08	MP014410
	M6 × 8	10	5.85	5.08	MP014411
	M6 × 10	10	5.85	5.08	MP014412
	M6 × 12	10	5.85	5.08	MP014413
	M6 × 16	10	5.85	5.08	MP014414
M6 × 20	10	5.85	5.08	MP014415	
M6 × 25	10	5.85	5.08	MP014416	

Hexagon Socket Head Screw **multicomp**PRO

Description	M	DK	K	S	Part Number
Hexagon Socket Head Screw, PVDF	M6 × 30	10	5.85	5.08	MP014417
	M6 × 35	10	5.85	5.08	MP014418
	M6 × 40	10	5.85	5.08	MP014419
	M6 × 45	10	5.85	5.08	MP014420
	M6 × 50	10	5.85	5.08	MP014421
	M8 × 10	13	7.82	6.08	MP014422
	M8 × 12	13	7.82	6.08	MP014423
	M8 × 16	13	7.82	6.08	MP014424
	M8 × 20	13	7.82	6.08	MP014425
	M8 × 25	13	7.82	6.08	MP014426
	M8 × 30	13	7.82	6.08	MP014427
	M8 × 35	13	7.82	6.08	MP014428
	M8 × 40	13	7.82	6.08	MP014429
	M8 × 45	13	7.82	6.08	MP014430
	M8 × 50	13	7.82	6.08	MP014431
M8 × 60	13	7.82	6.08	MP014432	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicompPRO