



### Heat shrinkable tubing 3:1 in a kit

#### ShrinkKit 321 Basic - black

The compact and handy kit belongs to the basic equipment for every assembler. Its ideal shrink ratio of 3:1 replaces many differently sized tubing.


#### Features and benefits

- Compact and handy kit
- Black tubing
- Available in a wide size range of 1.5 mm to 18.0 mm
- 220 precut pieces in five sizes
- Case can be re-used for storing nails, screws, nuts, fish hooks, etc.



ShrinkKit 321 Basic.

<b>MATERIAL</b>	Polyolefin, cross-linked (PO-X)
<b>Shrink Ratio</b>	3:1
<b>Operating Temperature</b>	-55 °C to +135 °C
<b>Min. Shrink Temperature</b>	+90 °C
<b>Longitudinal Change After Shrinkage</b>	+5 %/-10 % max.
<b>Dielectric Strength</b>	20 kV/mm according to ASTM D 2671
<b>Flammability</b>	self-extinguishing
<b>Insulation Class</b>	B (VDE 0530)



COMP.	Supplied Ø D min.	Recov. Ø d max.	Length (L)	Wall (WT)	Colour	Content	Tools	Article-No.
1	1.5	0.5	35.0	0.45	Black (BK)	50 pcs.	30-32	380-03001
2	6.0	2.0	35.0	0.70	Black (BK)	30 pcs.		
3	3.0	1.0	35.0	0.55	Black (BK)	25 pcs.		
4	6.0	2.0	35.0	0.70	Black (BK)	15 pcs.		
5	6.0	2.0	35.0	0.70	Black (BK)	15 pcs.		
6	3.0	1.0	35.0	0.55	Black (BK)	25 pcs.		
7	1.5	0.5	35.0	0.45	Black (BK)	50 pcs.		
8	12.0	4.0	80.0	0.70	Black (BK)	5 pcs.		
8	18.0	6.0	80.0	0.80	Black (BK)	5 pcs.		

All dimensions in mm. Subject to technical changes.

Recommended Tools			
	30 H5002	31 H5004	32 E4500
	561	561	560

For more information on toolings please refer to the Application Tooling chapter.



For product specific approvals and specifications please refer to the Appendix.