

START Surface IP44 DualTone

START Surface IP44 520lm 830/840 DualTone
0043425



Product features

- Ceiling / wall luminaire with integrated LED. Perfect solution for hallways, circulation spaces or foyer. Even and uniform light distribution with a halo lighting effect on the wall surface. Body Size diameter 180mm. Besa mounting box compatible, hole distance 51mm. DualTone functionality enables switch between 3000K and 4000K colour temperatures. Power 6W, output 520 lumens (4000K). Non-dimmable. IK03, IP44. Low maintenance with lifespan 90,000 hours L70:B50.



PRODUCT OVERVIEW

Product name	START Surface IP44 520lm 830/840 DualTone
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting
General application	Hospitality
ETIM Class	EC002892
E-number FI	4170568
Warranty	3 years
Fixture luminous flux (lm)	520
Luminaire efficacy (lm/W)	85
Colour temperature (K)	4000
Light colour	Amber White or Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	120
Photobiological Risk Group	RG0
Total power consumption (W)	6
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	No
Minimum dimming level (%)	100
LED Flickering Rate	High (>40%)
Housing colour	White
IP rating	IP44
IK rating	IK03
Product EAN number	5410288434254
Dimming method	N/A

DATA TABLE

General data

Product name	START Surface IP44 520lm 830/840 DualTone
Technology	LED

START Surface IP44 DualTone

START Surface IP44 520lm 830/840 DualTone
0043425

Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting
General application	Hospitality
Operating temperature range (°C)	-20°C - 40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4170568
Warranty	3 years

Optical data

Fixture luminous flux (lm)	520
Luminaire efficacy (lm/W)	85
Colour temperature (K)	4000
Correlated colour temperature range (K)	3000 - 4000
Light colour	Amber White or Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	120
Distribution type	Diffuse
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	6
Mains voltage (V)	220-240V
Lamp power factor	0.8
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	75
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	No
Minimum dimming level (%)	100
Drive current (mA)	19
Inrush Current (A)	0.5
Inrush Duration (µs)	30
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	F
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	High (>40%)
Max. Luminaires per 10A C Breaker	60
Max. Luminaires per 13A C Breaker	78
Max. Luminaires per 16A C Breaker	96
Max. Luminaires per 20A C Breaker	120
Max. Luminaires per 10A B Breaker	36
Max. Luminaires per 13A B Breaker	47
Max. Luminaires per 16A B Breaker	58
Max. Luminaires per 20A B Breaker	72

START Surface IP44 DualTone

START Surface IP44 520lm 830/840 DualTone
0043425

Lifetime data

Lifespan L70 B50	90000
Lifespan L80 B50	85000
Lifespan L90 B50	41000

Physical data

Housing colour	White
IP rating	IP44
IK rating	IK03
Diffuser finish	Opal
Diffuser material	Polypropylene
Nominal Product Height (mm)	75
Nominal Product Diameter (mm)	180
Weight (kg)	0.17


Packaging

Single packaging type	Carton
Product EAN number	5410288434254
Packaging single length / height (cm)	18.2
Packaging single width (cm)	7.8
Packaging single depth (cm)	18.2
DUN14 (outer)	15410288434251
Units per outer package	6
Packaging outer length / height (cm)	51.6
Packaging outer width (cm)	21.5
Packaging outer depth (cm)	22.0



Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

PHOTOMETRY



START Surface IP44 DualTone *START Surface IP44 520lm 830/840 DualTone* 0043425



TECHNICAL DRAWINGS

