

1040 MICRO CASE



KEY FEATURES

- WATERTIGHT, CRUSHPROOF & DUSTPROOF
- RUBBER LINER FOR EXTRA PROTECTION, DOUBLES AS O-RING SEAL
- EASY-OPEN LATCH
- AUTOMATIC PRESSURE EQUALISATION VALVE
- FREE CARABINER FOR EASY ATTACHMENT

1040	Length	Width	Depth	Lid	Base
INT. (mm)	161	95	44	18	26
EXT. (mm)	190	128	54		

WEIGHT (kg)

Empty: 0.30 With Foam: 0.34

SPECIFICATIONS

IP Rating: 67
Buoyancy: 0.60kg

Protection: Watertight, Crushproof, Dustproof

AVAILABLE COLOURS







SOLID YELLOW (with black liner)



CLEAR CASE (with black liner)



CLEAR CASE (with yellow liner)

PRODUCT ACCESSORIES

Pick 'N' Pluck™ Foam





LIFETIME GUARANTEE – All cases in the Peli™ Protector range are covered by the legendary Lifetime Guarantee. Simply put..."You break it, we replace it."