

EMI-Ferrite Bead

Automotive



AB0106BED-KIT JIS 1005, 1608 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance Ω (at 100MHz)	Tolerance ($\pm\%$)	RDC(Ω) Max.	Rated Current (mA)	Quantity
ABPY00100505100Y00	1.0	0.5	0.5	1005/0402	10	25	0.03	2000	20
ABSY00100505100Y00	1.0	0.5	0.5	1005/0402	10	25	0.025	1000	20
ABSY00100505220Y00	1.0	0.5	0.5	1005/0402	22	25	0.15	500	20
ABPY00100505300Y00	1.0	0.5	0.5	1005/0402	30	25	0.05	1700	20
ABSY00100505300Y00	1.0	0.5	0.5	1005/0402	30	25	0.2	500	20
ABUP00100505300Y00	1.0	0.5	0.5	1005/0402	30	25	0.022	3000	20
ABSY00100505330Y00	1.0	0.5	0.5	1005/0402	33	25	0.2	500	20
ABUP00100505330Y00	1.0	0.5	0.5	1005/0402	33	25	0.022	3000	20
ABSY00100505400Y00	1.0	0.5	0.5	1005/0402	40	25	0.2	500	20
ABNQ00100505470Y00	1.0	0.5	0.5	1005/0402	47	25	0.3	400	20
ABSY00100505470Y00	1.0	0.5	0.5	1005/0402	47	25	0.2	500	20
ABSY00100505500Y00	1.0	0.5	0.5	1005/0402	50	25	0.2	500	20
ABPY00100505600Y00	1.0	0.5	0.5	1005/0402	60	25	0.075	1500	20
ABSJ00100505600Y00	1.0	0.5	0.5	1005/0402	60	25	0.2	500	20
ABSY00100505600Y00	1.0	0.5	0.5	1005/0402	60	25	0.2	500	20
ABUP00100505600Y00	1.0	0.5	0.5	1005/0402	60	25	0.032	2500	20
ABSY00100505700Y00	1.0	0.5	0.5	1005/0402	70	25	0.15	600	20
ABNQ00100505750Y00	1.0	0.5	0.5	1005/0402	75	25	0.3	400	20
ABSY00100505800Y00	1.0	0.5	0.5	1005/0402	80	25	0.2	500	20
ABUP00100505800Y00	1.0	0.5	0.5	1005/0402	80	25	0.038	2300	20
ABSY00100505101Y00	1.0	0.5	0.5	1005/0402	100	25	0.25	500	20
ABNQ00100505121Y00	1.0	0.5	0.5	1005/0402	120	25	0.4	350	20
ABPY00100505121Y00	1.0	0.5	0.5	1005/0402	120	25	0.09	1400	20
ABSJ00100505121Y00	1.0	0.5	0.5	1005/0402	120	25	0.25	500	20
ABSY00100505121Y00	1.0	0.5	0.5	1005/0402	120	25	0.19	550	20
ABUP00100505121Y00	1.0	0.5	0.5	1005/0402	120	25	0.055	2000	20
ABSY00100505151Y00	1.0	0.5	0.5	1005/0402	150	25	0.4	400	20
ABPY00100505181Y00	1.0	0.5	0.5	1005/0402	180	25	0.14	900	20
ABSY00100505181Y00	1.0	0.5	0.5	1005/0402	180	25	0.4	400	20
ABNQ00100505221Y00	1.0	0.5	0.5	1005/0402	220	25	0.6	200	20
ABPY00100505221Y00	1.0	0.5	0.5	1005/0402	220	25	0.18	1100	20
ABSY00100505221Y00	1.0	0.5	0.5	1005/0402	220	25	0.29	450	20
ABSY00100505241Y00	1.0	0.5	0.5	1005/0402	240	25	0.4	400	20
ABSJ00100505301Y00	1.0	0.5	0.5	1005/0402	300	25	0.5	300	20
ABSY00100505301Y00	1.0	0.5	0.5	1005/0402	300	25	0.5	300	20
ABSY00100505471Y00	1.0	0.5	0.5	1005/0402	470	25	0.5	300	20
ABSJ00100505481Y00	1.0	0.5	0.5	1005/0402	480	25	0.5	300	20
ABSY00100505481Y00	1.0	0.5	0.5	1005/0402	480	25	0.5	300	20
ABPY00100505601Y00	1.0	0.5	0.5	1005/0402	600	25	0.34	700	20
ABSJ00100505601Y00	1.0	0.5	0.5	1005/0402	600	25	0.6	300	20
ABSY00100505601Y00	1.0	0.5	0.5	1005/0402	600	25	0.52	300	20
ABPY00100505102Y00	1.0	0.5	0.5	1005/0402	1000	25	0.49	500	20
ABSJ00100505102Y00	1.0	0.5	0.5	1005/0402	1000	25	0.95	200	20
ABSY00100505102Y00	1.0	0.5	0.5	1005/0402	1000	25	0.65	300	20
ABBK00160808100Y00	1.6	0.8	0.8	1608/0603	10	25	0.05	500	20
ABGK00160808100Y00	1.6	0.8	0.8	1608/0603	10	25	0.3	600	20
ABPY00160808100Y00	1.6	0.8	0.8	1608/0603	10	25	0.02	4000	20
ABBK00160808300Y00	1.6	0.8	0.8	1608/0603	30	25	0.1	400	20
ABGK00160808300Y00	1.6	0.8	0.8	1608/0603	30	25	0.06	800	20
ABPY00160808300Y00	1.6	0.8	0.8	1608/0603	30	25	0.03	3000	20

EMI-Ferrite Bead

Automotive



AB0106BED-KIT JIS 1005, 1608 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance Ω (at 100MHz)	Tolerance ($\pm\%$)	RDC(Ω) Max.	Rated Current (mA)	Quantity
ABUP00160808300Y00	1.6	0.8	0.8	1608/0603	30	25	0.015	4500	20
ABBK00160808600Y00	1.6	0.8	0.8	1608/0603	60	25	0.1	400	20
ABGK00160808600Y00	1.6	0.8	0.8	1608/0603	60	25	0.06	700	20
ABNQ00160808600Y00	1.6	0.8	0.8	1608/0603	60	25	0.25	500	20
ABPY00160808600Y00	1.6	0.8	0.8	1608/0603	60	25	0.04	3000	20
ABBK00160808800Y00	1.6	0.8	0.8	1608/0603	80	25	0.15	400	20
ABGK00160808800Y00	1.6	0.8	0.8	1608/0603	80	25	0.1	600	20
ABPY00160808800Y00	1.6	0.8	0.8	1608/0603	80	25	0.05	2500	20
ABUP00160808101Y00	1.6	0.8	0.8	1608/0603	100	25	0.03	3000	20
ABBK00160808121Y00	1.6	0.8	0.8	1608/0603	120	25	0.25	400	20
ABGK00160808121Y00	1.6	0.8	0.8	1608/0603	120	25	0.15	600	20
ABNQ00160808121Y00	1.6	0.8	0.8	1608/0603	120	25	0.3	400	20
ABPY00160808121Y00	1.6	0.8	0.8	1608/0603	120	25	0.08	2500	20
ABSJ00160808121Y00	1.6	0.8	0.8	1608/0603	120	25	0.25	400	20
ABUP00160808121Y00	1.6	0.8	0.8	1608/0603	120	25	0.03	3000	20
ABBK00160808181Y00	1.6	0.8	0.8	1608/0603	180	25	0.3	300	20
ABPY00160808181Y00	1.6	0.8	0.8	1608/0603	180	25	0.09	2000	20
ABUP00160808181Y00	1.6	0.8	0.8	1608/0603	180	25	0.05	2000	20
ABGK00160808201Y00	1.6	0.8	0.8	1608/0603	200	25	0.18	400	20
ABBK00160808221Y00	1.6	0.8	0.8	1608/0603	220	25	0.3	300	20
ABGK00160808221Y00	1.6	0.8	0.8	1608/0603	220	25	0.18	550	20
ABPY00160808221Y00	1.6	0.8	0.8	1608/0603	220	25	0.1	2000	20
ABUP00160808221Y00	1.6	0.8	0.8	1608/0603	220	25	0.04	2500	20
ABBK00160808301Y00	1.6	0.8	0.8	1608/0603	300	25	0.4	300	20
ABGK00160808301Y00	1.6	0.8	0.8	1608/0603	300	25	0.25	500	20
ABNQ00160808301Y00	1.6	0.8	0.8	1608/0603	300	25	0.4	400	20
ABPY00160808301Y00	1.6	0.8	0.8	1608/0603	300	25	0.12	1500	20
ABBK00160808471Y00	1.6	0.8	0.8	1608/0603	470	25	0.5	300	20
ABGK00160808471Y00	1.6	0.8	0.8	1608/0603	470	25	0.3	400	20
ABPY00160808471Y00	1.6	0.8	0.8	1608/0603	470	25	0.15	1500	20
ABBK00160808601Y00	1.6	0.8	0.8	1608/0603	600	25	0.5	300	20
ABGK00160808601Y00	1.6	0.8	0.8	1608/0603	600	25	0.3	400	20
ABPY00160808601Y00	1.6	0.8	0.8	1608/0603	600	25	0.2	1000	20
ABSJ00160808601Y00	1.6	0.8	0.8	1608/0603	600	25	0.4	400	20
ABBK00160808102Y00	1.6	0.8	0.8	1608/0603	1000	25	0.6	300	20
ABGK00160808102Y00	1.6	0.8	0.8	1608/0603	1000	25	0.45	300	20
ABNQ00160808102Y00	1.6	0.8	0.8	1608/0603	1000	25	0.6	200	20
ABPY00160808102Y00	1.6	0.8	0.8	1608/0603	1000	25	0.25	800	20
ABSJ00160808102Y00	1.6	0.8	0.8	1608/0603	1000	25	0.6	300	20

EMI-Ferrite Bead

Automotive



AB0106BED-KIT JIS 1005, 1608 Size

Dimensions – Millimeters (Inches)

