

RF Inductor-Wirewound

Automotive



AWS10JRF0-KIT JIS 1005 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω) Max.	IDC(mA)Max.	Quantity
AWCS001207071N0J00	1.1	0.6	0.6	1005/0402	1	5	0.045	1360	20
AWCS001207071N2J00	1.1	0.6	0.6	1005/0402	1.2	5	0.14	640	20
AWCS001207071N9J00	1.1	0.6	0.6	1005/0402	1.9	5	0.07	1040	20
AWCS001207072N0J00	1.1	0.6	0.6	1005/0402	2	5	0.07	1040	20
AWCS001207072N2J00	1.1	0.6	0.6	1005/0402	2.2	5	0.07	960	20
AWCS001207072N4J00	1.1	0.6	0.6	1005/0402	2.4	5	0.068	790	20
AWCS001207072N5J00	1.1	0.6	0.6	1005/0402	2.5	5	0.15	640	20
AWCS001207072N7J00	1.1	0.6	0.6	1005/0402	2.7	5	0.12	640	20
AWCS001207073N3J00	1.1	0.6	0.6	1005/0402	3.3	5	0.066	840	20
AWCS001207073N6J00	1.1	0.6	0.6	1005/0402	3.6	5	0.066	840	20
AWCS001207073N9J00	1.1	0.6	0.6	1005/0402	3.9	5	0.066	840	20
AWCS001207074N3J00	1.1	0.6	0.6	1005/0402	4.3	5	0.091	700	20
AWCS001207074N7J00	1.1	0.6	0.6	1005/0402	4.7	5	0.13	640	20
AWCS001207075N1J00	1.1	0.6	0.6	1005/0402	5.1	5	0.083	800	20
AWCS001207075N6J00	1.1	0.6	0.6	1005/0402	5.6	5	0.083	760	20
AWCS001207075N8J00	1.1	0.6	0.6	1005/0402	5.8	5	0.083	760	20
AWCS001207076N2J00	1.1	0.6	0.6	1005/0402	6.2	5	0.083	760	20
AWCS001207076N8J00	1.1	0.6	0.6	1005/0402	6.8	5	0.083	680	20
AWCS001207077N3J00	1.1	0.6	0.6	1005/0402	7.3	5	0.12	680	20
AWCS001207077N5J00	1.1	0.6	0.6	1005/0402	7.5	5	0.1	680	20
AWCS001207078N2J00	1.1	0.6	0.6	1005/0402	8.2	5	0.1	680	20
AWCS001207078N7J00	1.1	0.6	0.6	1005/0402	8.7	5	0.2	480	20
AWCS001207079N0J00	1.1	0.6	0.6	1005/0402	9	5	0.1	680	20
AWCS001207079N1J00	1.1	0.6	0.6	1005/0402	9.1	5	0.1	680	20
AWCS001207079N5J00	1.1	0.6	0.6	1005/0402	9.5	5	0.2	480	20
AWCS0012070710NJ00	1.1	0.6	0.6	1005/0402	10	5	0.2	480	20
AWCS0012070711NJ00	1.1	0.6	0.6	1005/0402	11	5	0.12	640	20
AWCS0012070712NJ00	1.1	0.6	0.6	1005/0402	12	5	0.12	640	20
AWCS0012070713NJ00	1.1	0.6	0.6	1005/0402	13	5	0.21	440	20
AWCS0012070715NJ00	1.1	0.6	0.6	1005/0402	15	5	0.17	560	20
AWCS0012070716NJ00	1.1	0.6	0.6	1005/0402	16	5	0.22	560	20
AWCS0012070718NJ00	1.1	0.6	0.6	1005/0402	18	5	0.23	420	20
AWCS0012070719NJ00	1.1	0.6	0.6	1005/0402	19	5	0.2	480	20
AWCS0012070720NJ00	1.1	0.6	0.6	1005/0402	20	5	0.25	420	20
AWCS0012070722NJ00	1.1	0.6	0.6	1005/0402	22	5	0.3	400	20
AWCS0012070723NJ00	1.1	0.6	0.6	1005/0402	23	5	0.3	400	20
AWCS0012070724NJ00	1.1	0.6	0.6	1005/0402	24	5	0.3	400	20
AWCS0012070727NJ00	1.1	0.6	0.6	1005/0402	27	5	0.3	400	20
AWCS0012070730NJ00	1.1	0.6	0.6	1005/0402	30	5	0.35	400	20
AWCS0012070733NJ00	1.1	0.6	0.6	1005/0402	33	5	0.4	400	20
AWCS0012070736NJ00	1.1	0.6	0.6	1005/0402	36	5	0.44	320	20
AWCS0012070739NJ00	1.1	0.6	0.6	1005/0402	39	5	0.55	200	20
AWCS0012070740NJ00	1.1	0.6	0.6	1005/0402	40	5	0.65	320	20
AWCS0012070743NJ00	1.1	0.6	0.6	1005/0402	43	5	0.81	100	20
AWCS0012070747NJ00	1.1	0.6	0.6	1005/0402	47	5	0.83	150	20
AWCS0012070751NJ00	1.1	0.6	0.6	1005/0402	51	5	0.82	100	20
AWCS0012070756NJ00	1.1	0.6	0.6	1005/0402	56	5	0.97	100	20
AWCS0012070768NJ00	1.1	0.6	0.6	1005/0402	68	5	1.12	100	20
AWCS0012070772NJ00	1.1	0.6	0.6	1005/0402	72	5	2	30	20
AWCS0012070782NJ00	1.1	0.6	0.6	1005/0402	82	5	1.55	50	20

RF Inductor-Wirewound

Automotive



AWS10JRF0-KIT JIS 1005 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω) Max.	IDC(mA)Max.	Quantity
AWCS00120707R10J00	1.1	0.6	0.6	1005/0402	100	5	2	30	20
AWCS00120707R18J00	1.1	0.6	0.6	1005/0402	180	5	2.7	50	20
AWCS00120707R22J00	1.1	0.6	0.6	1005/0402	220	5	4	50	20

RF Inductor-Wirewound

Automotive



AWS10JRF0-KIT JIS 1005 Size

Dimensions – Millimeters (Inches)

