

RF Inductor-Wirewound



BWS25JRF0-KIT JIS 2520 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω) Max.	IDC(mA)Max.	Quantity
BWCS0029282110NJ00	2.9	2.7	2.1	2520/1008	10	5	0.08	1000	20
BWCS0029282112NJ00	2.9	2.7	2.1	2520/1008	12	5	0.09	1000	20
BWCS0029282115NJ00	2.9	2.7	2.1	2520/1008	15	5	0.1	1000	20
BWCS0029282118NJ00	2.9	2.7	2.1	2520/1008	18	5	0.11	1000	20
BWCS0029282122NJ00	2.9	2.7	2.1	2520/1008	22	5	0.12	1000	20
BWCS0029282127NJ00	2.9	2.7	2.1	2520/1008	27	5	0.13	1000	20
BWCS0029282133NJ00	2.9	2.7	2.1	2520/1008	33	5	0.14	1000	20
BWCS0029282139NJ00	2.9	2.7	2.1	2520/1008	39	5	0.15	1000	20
BWCS0029282147NJ00	2.9	2.7	2.1	2520/1008	47	5	0.16	1000	20
BWCS0029282156NJ00	2.9	2.7	2.1	2520/1008	56	5	0.18	1000	20
BWCS0029282182NJ00	2.9	2.7	2.1	2520/1008	82	5	0.22	1000	20
BWCS00292821R10J00	2.9	2.7	2.1	2520/1008	100	5	0.56	650	20
BWCS00292821R12J00	2.9	2.7	2.1	2520/1008	120	5	0.63	650	20
BWCS00292821R15J00	2.9	2.7	2.1	2520/1008	150	5	0.7	580	20
BWCS00292821R18J00	2.9	2.7	2.1	2520/1008	180	5	0.77	620	20
BWCS00292821R20J00	2.9	2.7	2.1	2520/1008	200	5	0.84	500	20
BWCS00292821R22J00	2.9	2.7	2.1	2520/1008	220	5	0.84	500	20
BWCS00292821R27J00	2.9	2.7	2.1	2520/1008	270	5	0.91	500	20
BWCS00292821R33J00	2.9	2.7	2.1	2520/1008	330	5	1.05	450	20
BWCS00292821R39J00	2.9	2.7	2.1	2520/1008	390	5	1.12	470	20
BWCS00292821R47J00	2.9	2.7	2.1	2520/1008	470	5	1.19	470	20
BWCS00292821R56J00	2.9	2.7	2.1	2520/1008	560	5	1.33	400	20
BWCS00292821R62J00	2.9	2.7	2.1	2520/1008	620	5	1.4	300	20
BWCS00292821R68J00	2.9	2.7	2.1	2520/1008	680	5	1.47	400	20
BWCS00292821R75J00	2.9	2.7	2.1	2520/1008	750	5	1.54	360	20
BWCS00292821R82J00	2.9	2.7	2.1	2520/1008	820	5	1.61	400	20
BWCS00292821R91J00	2.9	2.7	2.1	2520/1008	910	5	1.68	380	20
BWCS002928211R0J00	2.9	2.7	2.1	2520/1008	1000	5	1.75	370	20
BWCS002928211R2J00	2.9	2.7	2.1	2520/1008	1200	5	2	310	20
BWCS002928211R5J00	2.9	2.7	2.1	2520/1008	1500	5	2.3	330	20
BWCS002928211R8J00	2.9	2.7	2.1	2520/1008	1800	5	2.6	300	20
BWCS002928212R2J00	2.9	2.7	2.1	2520/1008	2200	5	2.8	280	20
BWCS002928212R7J00	2.9	2.7	2.1	2520/1008	2700	5	3.2	290	20
BWCS002928213R3J00	2.9	2.7	2.1	2520/1008	3300	5	3.4	290	20
BWCS002928213R9J00	2.9	2.7	2.1	2520/1008	3900	5	3.6	260	20
BWCS002928214R7J00	2.9	2.7	2.1	2520/1008	4700	5	4	260	20
BWCS002928215R6J00	2.9	2.7	2.1	2520/1008	5600	5	4	240	20
BWCS002928216R8J00	2.9	2.7	2.1	2520/1008	6800	5	4.9	200	20
BWCS002928218R2J00	2.9	2.7	2.1	2520/1008	8200	5	6	170	20
BWCS00292821100J00	2.9	2.7	2.1	2520/1008	10000	5	8	150	20
BWCS00292821150J00	2.9	2.7	2.1	2520/1008	15000	5	11	100	20
BWLS003025221R2J00	2.9	2.5	2.2	2520/1008	1.2	5	0.5	1200	20
BWLS003025221R5J00	2.9	2.5	2.2	2520/1008	1.5	5	0.65	1200	20
BWLS003025221R8J00	2.9	2.5	2.2	2520/1008	1.8	5	0.75	1050	20
BWLS003025222R2J00	2.9	2.5	2.2	2520/1008	2.2	5	0.9	950	20
BWLS003025222R7J00	2.9	2.5	2.2	2520/1008	2.7	5	1	950	20
BWLS003025223R3J00	2.9	2.5	2.2	2520/1008	3.3	5	1.15	900	20
BWLS003025223R9J00	2.9	2.5	2.2	2520/1008	3.9	5	1.25	850	20
BWLS003025224R7J00	2.9	2.5	2.2	2520/1008	4.7	5	1.35	700	20
BWLS003025225R6J00	2.9	2.5	2.2	2520/1008	5.6	5	1.45	700	20

RF Inductor-Wirewound



BWS25JRF0-KIT JIS 2520 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω) Max.	IDC(mA)Max.	Quantity
BWLS003025226R8J00	2.9	2.5	2.2	2520/1008	6.8	5	1.6	600	20
BWLS003025228R2J00	2.9	2.5	2.2	2520/1008	8.2	5	1.8	550	20
BWLS00302522100J00	2.9	2.5	2.2	2520/1008	10	5	2.4	500	20
BWLS00302522120J00	2.9	2.5	2.2	2520/1008	12	5	2.4	450	20
BWLS00302522150J00	2.9	2.5	2.2	2520/1008	15	5	2.4	450	20
BWLS00302522390J00	2.9	2.5	2.2	2520/1008	39	5	10	170	20

RF Inductor-Wirewound



BWS25JRF0-KIT JIS 2520 Size

Dimensions – Millimeters (Inches)

2520

