

EMI-Ferrite Bead



BB0160BED-KIT JIS 1608 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance Ω (at 100MHz)	Tolerance ($\pm\%$)	RDC(Ω) Max.	Rated Current (mA)	Quantity
BBBK00160808100Y00	1.6	0.8	0.8	1608	10	25	0.05	500	20
BBBK00160808100Y00	1.6	0.8	0.8	1608	10	25	0.05	500	20
BBGK00160808100Y00	1.6	0.8	0.8	1608	10	25	0.03	1000	20
BBHV00160808100Y00	1.6	0.8	0.8	1608	10	25	0.01	6000	20
BBPY00160808100Y00	1.6	0.8	0.8	1608	10	25	0.02	4000	20
BBBK00160808110Y00	1.6	0.8	0.8	1608	11	25	0.05	500	20
BBGK00160808110Y00	1.6	0.8	0.8	1608	11	25	0.03	1000	20
BBPY00160808110Y00	1.6	0.8	0.8	1608	11	25	0.02	4000	20
BBPY00160808190Y00	1.6	0.8	0.8	1608	19	25	0.03	3000	20
BBPY00160808220Y00	1.6	0.8	0.8	1608	22	25	0.03	3000	20
BBPY00160808250Y00	1.6	0.8	0.8	1608	25	25	0.03	3000	20
BBUP00160805260Y00	1.6	0.8	0.5	1608	26	25	0.007	6000	20
BBPY00160808260Y00	1.6	0.8	0.8	1608	26	25	0.03	3000	20
BBUP00160805300Y00	1.6	0.8	0.5	1608	30	25	0.007	6000	20
BBBK00160808300Y00	1.6	0.8	0.8	1608	30	25	0.1	400	20
BBGK00160808300Y00	1.6	0.8	0.8	1608	30	25	0.06	800	20
BBHV00160808300Y00	1.6	0.8	0.8	1608	30	25	0.015	4000	20
BBPY00160808300Y00	1.6	0.8	0.8	1608	30	25	0.03	3000	20
BBUP00160808300Y00	1.6	0.8	0.8	1608	30	25	0.015	4500	20
BBBK00160808310Y00	1.6	0.8	0.8	1608	31	25	0.1	400	20
BBPY00160808330Y00	1.6	0.8	0.8	1608	33	25	0.035	3000	20
BBGK00160808400Y00	1.6	0.8	0.8	1608	40	25	0.06	800	20
BBPY00160808400Y00	1.6	0.8	0.8	1608	40	25	0.035	3000	20
BBPY00160808470Y00	1.6	0.8	0.8	1608	47	25	0.04	3000	20
BBGK00160808500Y00	1.6	0.8	0.8	1608	50	25	0.06	800	20
BBPY00160808500Y00	1.6	0.8	0.8	1608	50	25	0.04	3000	20
BBUP00160805600Y00	1.6	0.8	0.5	1608	60	25	0.02	4000	20
BBUP00160805600Y00	1.6	0.8	0.5	1608	60	25	0.02	4000	20
BBBK00160808600Y00	1.6	0.8	0.8	1608	60	25	0.1	400	20
BBGK00160808600Y00	1.6	0.8	0.8	1608	60	25	0.06	700	20
BBHV00160808600Y00	1.6	0.8	0.8	1608	60	25	0.03	3000	20
BBNQ00160808600Y00	1.6	0.8	0.8	1608	60	25	0.25	500	20
BBPY00160808600Y00	1.6	0.8	0.8	1608	60	25	0.04	3000	20
BBSJ00160808600Y00	1.6	0.8	0.8	1608	60	25	0.1	400	20
BBUP00160808600Y00	1.6	0.8	0.8	1608	60	25	0.02	4000	20
BBPY00160808680Y00	1.6	0.8	0.8	1608	68	25	0.05	2500	20
BBPY00160808680Y00	1.6	0.8	0.8	1608	68	25	0.05	2500	20
BBUP00160805700Y00	1.6	0.8	0.5	1608	70	25	0.02	4000	20
BBGK00160808700Y00	1.6	0.8	0.8	1608	70	25	0.1	600	20
BBPY00160808700Y00	1.6	0.8	0.8	1608	70	25	0.05	2500	20
BBPY00160808700Y00	1.6	0.8	0.8	1608	70	25	0.05	2500	20
BBUP00160808700Y00	1.6	0.8	0.8	1608	70	25	0.02	4000	20
BBNQ00160808750Y00	1.6	0.8	0.8	1608	75	25	0.25	500	20
BBPY00160808750Y00	1.6	0.8	0.8	1608	75	25	0.05	2500	20
BBPY00160808750Y00	1.6	0.8	0.8	1608	75	25	0.05	2500	20
BBBK00160808800Y00	1.6	0.8	0.8	1608	80	25	0.15	400	20
BBGK00160808800Y00	1.6	0.8	0.8	1608	80	25	0.1	600	20
BBPY00160808800Y00	1.6	0.8	0.8	1608	80	25	0.05	2500	20
BBUP00160805101Y00	1.6	0.8	0.5	1608	100	25	0.025	3000	20
BBUP00160805101Y00	1.6	0.8	0.5	1608	100	25	0.025	3000	20

EMI-Ferrite Bead



BB0160BED-KIT JIS 1608 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance Ω (at 100MHz)	Tolerance ($\pm\%$)	RDC(Ω) Max.	Rated Current (mA)	Quantity
BBBK00160808101Y00	1.6	0.8	0.8	1608	100	25	0.2	400	20
BBGK00160808101Y00	1.6	0.8	0.8	1608	100	25	0.15	600	20
BBPY00160808101Y00	1.6	0.8	0.8	1608	100	25	0.05	2500	20
BBUP00160808101Y00	1.6	0.8	0.8	1608	100	25	0.03	3000	20
BBUP00160805121Y00	1.6	0.8	0.5	1608	120	25	0.025	3000	20
BBBK00160808121Y00	1.6	0.8	0.8	1608	120	25	0.25	400	20
BBGK00160808121Y00	1.6	0.8	0.8	1608	120	25	0.15	600	20
BBHV00160808121Y00	1.6	0.8	0.8	1608	120	25	0.04	3000	20
BBNQ00160808121Y00	1.6	0.8	0.8	1608	120	25	0.3	400	20
BBNQ00160808121Y00	1.6	0.8	0.8	1608	120	25	0.3	400	20
BBPY00160808121Y00	1.6	0.8	0.8	1608	120	25	0.08	2500	20
BBSJ00160808121Y00	1.6	0.8	0.8	1608	120	25	0.25	400	20
BBUP00160808121Y00	1.6	0.8	0.8	1608	120	25	0.03	3000	20
BBGK00160808151Y00	1.6	0.8	0.8	1608	150	25	0.15	600	20
BBPY00160808151Y00	1.6	0.8	0.8	1608	150	25	0.085	2000	20
BBGK00160808181Y00	1.6	0.8	0.8	1608	180	25	0.18	400	20
BBPY00160808181Y00	1.6	0.8	0.8	1608	180	25	0.09	2000	20
BBUP00160808181Y00	1.6	0.8	0.8	1608	180	25	0.05	2000	20
BBGK00160808201Y00	1.6	0.8	0.8	1608	200	25	0.18	400	20
BBHV00160808201Y00	1.6	0.8	0.8	1608	200	25	0.05	2500	20
BBPY00160808201Y00	1.6	0.8	0.8	1608	200	25	0.095	2000	20
BBUP00160805221Y00	1.6	0.8	0.5	1608	220	25	0.04	2500	20
BBBK00160808221Y00	1.6	0.8	0.8	1608	220	25	0.3	300	20
BBGK00160808221Y00	1.6	0.8	0.8	1608	220	25	0.18	550	20
BBHV00160808221Y00	1.6	0.8	0.8	1608	220	25	0.08	2000	20
BBPY00160808221Y00	1.6	0.8	0.8	1608	220	25	0.1	2000	20
BBUP00160808221Y00	1.6	0.8	0.8	1608	220	25	0.04	2500	20
BBNQ00160808241Y00	1.6	0.8	0.8	1608	240	25	0.35	400	20
BBPY00160808241Y00	1.6	0.8	0.8	1608	240	25	0.12	1500	20
BBBK00160808301Y00	1.6	0.8	0.8	1608	300	25	0.4	300	20
BBGK00160808301Y00	1.6	0.8	0.8	1608	300	25	0.25	500	20
BBHV00160808301Y00	1.6	0.8	0.8	1608	300	25	0.08	2000	20
BBNQ00160808301Y00	1.6	0.8	0.8	1608	300	25	0.4	400	20
BBPY00160808301Y00	1.6	0.8	0.8	1608	300	25	0.12	1500	20
BBUP00160805331Y00	1.6	0.8	0.5	1608	330	25	0.07	1500	20
BBGK00160808331Y00	1.6	0.8	0.8	1608	330	25	0.3	400	20
BBHV00160808331Y00	1.6	0.8	0.8	1608	330	25	0.08	2000	20
BBPY00160808331Y00	1.6	0.8	0.8	1608	330	25	0.12	1500	20
BBBK00160808471Y00	1.6	0.8	0.8	1608	470	25	0.5	300	20
BBGK00160808471Y00	1.6	0.8	0.8	1608	470	25	0.3	400	20
BBHV00160808471Y00	1.6	0.8	0.8	1608	470	25	0.1	2000	20
BBPY00160808471Y00	1.6	0.8	0.8	1608	470	25	0.15	1500	20
BBBK00160808601Y00	1.6	0.8	0.8	1608	600	25	0.5	300	20
BBGK00160808601Y00	1.6	0.8	0.8	1608	600	25	0.3	400	20
BBHV00160808601Y00	1.6	0.8	0.8	1608	600	25	0.1	2000	20
BBPY00160808601Y00	1.6	0.8	0.8	1608	600	25	0.2	1000	20
BBSJ00160808601Y00	1.6	0.8	0.8	1608	600	25	0.4	400	20
BBBK00160808102Y00	1.6	0.8	0.8	1608	1000	25	0.6	300	20
BBGK00160808102Y00	1.6	0.8	0.8	1608	1000	25	0.45	300	20
BBNQ00160808102Y00	1.6	0.8	0.8	1608	1000	25	0.6	200	20

EMI-Ferrite Bead



BB0160BED-KIT JIS 1608 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance Ω (at 100MHz)	Tolerance ($\pm\%$)	RDC(Ω) Max.	Rated Current (mA)	Quantity
BBPY00160808102Y00	1.6	0.8	0.8	1608	1000	25	0.25	800	20
BBSJ00160808102Y00	1.6	0.8	0.8	1608	1000	25	0.6	300	20
BBBK00160808152Y00	1.6	0.8	0.8	1608	1500	25	0.6	300	20
BBGK00160808152Y00	1.6	0.8	0.8	1608	1500	25	0.7	150	20
BBPY00160808152Y00	1.6	0.8	0.8	1608	1500	25	0.4	500	20
BBBK00160808202Y00	1.6	0.8	0.8	1608	2000	25	0.8	200	20
BBSJ00160808202Y00	1.6	0.8	0.8	1608	2000	25	1	200	20
BBSJ00160808222Y00	1.6	0.8	0.8	1608	2200	25	1	200	20

EMI-Ferrite Bead



BB0160BED-KIT JIS 1608 Size

Dimensions – Millimeters (Inches)

