

RF Inductor-Wirewound



BWS10GRF0-KIT JIS 1005 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω) Max.	IDC(mA)Max.	Quantity
BWCS0012070710NG00	1.1	0.6	0.6	1005/0402	10	2	0.2	480	20
BWCS0012070711NG00	1.1	0.6	0.6	1005/0402	11	2	0.12	640	20
BWCS0012070712NG00	1.1	0.6	0.6	1005/0402	12	2	0.12	640	20
BWCS0012070713NG00	1.1	0.6	0.6	1005/0402	13	2	0.21	440	20
BWCS0012070715NG00	1.1	0.6	0.6	1005/0402	15	2	0.17	560	20
BWCS0012070716NG00	1.1	0.6	0.6	1005/0402	16	2	0.22	560	20
BWCS0012070718NG00	1.1	0.6	0.6	1005/0402	18	2	0.23	420	20
BWCS0012070719NG00	1.1	0.6	0.6	1005/0402	19	2	0.2	480	20
BWCS0012070720NG00	1.1	0.6	0.6	1005/0402	20	2	0.25	420	20
BWCS0012070722NG00	1.1	0.6	0.6	1005/0402	22	2	0.3	400	20
BWCS0012070723NG00	1.1	0.6	0.6	1005/0402	23	2	0.3	400	20
BWCS0012070724NG00	1.1	0.6	0.6	1005/0402	24	2	0.3	400	20
BWCS0012070727NG00	1.1	0.6	0.6	1005/0402	27	2	0.3	400	20
BWCS0012070730NG00	1.1	0.6	0.6	1005/0402	30	2	0.35	400	20
BWCS0012070733NG00	1.1	0.6	0.6	1005/0402	33	2	0.4	400	20
BWCS0012070736NG00	1.1	0.6	0.6	1005/0402	36	2	0.44	320	20
BWCS0012070739NG00	1.1	0.6	0.6	1005/0402	39	2	0.55	200	20
BWCS0012070740NG00	1.1	0.6	0.6	1005/0402	40	2	0.65	320	20
BWCS0012070743NG00	1.1	0.6	0.6	1005/0402	43	2	0.81	100	20
BWCS0012070747NG00	1.1	0.6	0.6	1005/0402	47	2	0.83	150	20
BWCS0012070751NG00	1.1	0.6	0.6	1005/0402	51	2	0.82	100	20
BWCS0012070756NG00	1.1	0.6	0.6	1005/0402	56	2	0.97	100	20
BWCS0012070768NG00	1.1	0.6	0.6	1005/0402	68	2	1.12	100	20
BWCS0012070772NG00	1.1	0.6	0.6	1005/0402	72	2	2	30	20
BWCS0012070782NG00	1.1	0.6	0.6	1005/0402	82	2	1.55	50	20
BWCS00120707R10G00	1.1	0.6	0.6	1005/0402	100	2	2	30	20
BWCS00120707R18G00	1.1	0.6	0.6	1005/0402	180	2	2.7	50	20
BWCS00120707R22G00	1.1	0.6	0.6	1005/0402	220	2	4	50	20

RF Inductor-Wirewound



BWS10GRF0-KIT JIS 1005 Size

Dimensions – Millimeters (Inches)

1005

