

BWV320PWR-KIT JIS 3225 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω)	IDC(mA)Max.	Quantity
BWVN00322515R47T00	3.2	2.5	1.5	3225	0.47	30	0.03	2.55	20
BWVN003225151R0T00	3.2	2.5	1.5	3225	1	30	0.045	2.05	20
BWVN003225151R5T00	3.2	2.5	1.5	3225	1.5	30	0.057	1.75	20
BWVN003225152R2M00	3.2	2.5	1.5	3225	2.2	20	0.076	1.6	20
BWVN003225152R2T00	3.2	2.5	1.5	3225	2.2	30	0.076	1.6	20
BWVN003225153R3M00	3.2	2.5	1.5	3225	3.3	20	0.12	1.2	20
BWVN003225153R3T00	3.2	2.5	1.5	3225	3.3	30	0.12	1.2	20
BWVN003225154R7M00	3.2	2.5	1.5	3225	4.7	20	0.18	1	20
BWVN003225154R7T00	3.2	2.5	1.5	3225	4.7	30	0.18	1	20
BWVN003225156R8M00	3.2	2.5	1.5	3225	6.8	20	0.24	0.85	20
BWVN003225156R8T00	3.2	2.5	1.5	3225	6.8	30	0.24	0.85	20
BWVN00322515100M00	3.2	2.5	1.5	3225	10	20	0.38	0.7	20
BWVN00322515100T00	3.2	2.5	1.5	3225	10	30	0.38	0.7	20
BWVN00322515150M00	3.2	2.5	1.5	3225	15	20	0.7	0.5	20
BWVN00322515150T00	3.2	2.5	1.5	3225	15	30	0.7	0.5	20
BWVN00322515220M00	3.2	2.5	1.5	3225	22	20	0.81	0.45	20
BWVN00322515220T00	3.2	2.5	1.5	3225	22	30	0.81	0.45	20
BWVN00322515330M00	3.2	2.5	1.5	3225	33	20	1.05	0.32	20
BWVN00322515330T00	3.2	2.5	1.5	3225	33	30	1.05	0.32	20
BWVN00322515470M00	3.2	2.5	1.5	3225	47	20	1.48	0.24	20
BWVN00322515470T00	3.2	2.5	1.5	3225	47	30	1.48	0.24	20

Power Inductor-Wirewound



BWV320PWR-KIT JIS 3225 Size

Dimensions – Millimeters (Inches)

3225

