


# **ENERGIZER A93**



### **Industry Standard Dimensions**



### **General Information**

C

Classification: Alkaline

**Chemical System:** Zinc-Manganese Dioxide (Zn/MnO<sub>2</sub>)

No added mercury or cadmium

**Designation:** ANSI-14A, IEC-LR14

Nominal Voltage: 1.5 volts


**Operating Temp:** -18°C to 55°C (0°F to 130°F)

**Typical Weight:** 66 grams

Typical Volume: 27 cubic centimeters
Shelf Life: 10 years at 21°C
Terminal: Flat Contact

## **Performance Comparison**


A93 vs. Typical Carbon Zinc (C) at 21°C



**Industry Standard Testing Protocol** 

#### **Device Selection Guide:**

#### **Battery Selection Indicator**



**Important Notice** 

This datasheet contains typical information specific to products manufactured at the time of its publication.

Contents herein do not constitute a warranty and are for reference only.

Form No. A93GL1019 Page 1 of 1