


ENERGIZER A95





Industry Standard Dimensions



General Information

Classification: Alkaline

Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

No added mercury or cadmium

Designation: ANSI-13A, IEC-LR20

Nominal Voltage: 1.5 volts


Operating Temp: -18°C to 55°C (0°F to 130°F)

Typical Weight: 139 grams

Typical Volume: 56 cubic centimeters **Shelf Life:** 10 years at 21°C **Terminal:** Flat Contact

Performance Comparison


A95 vs. Typical Carbon Zinc (D) at 21°C



Industry Standard Testing Protocol

Device Selection Guide:

Battery Selection Indicator



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

Contents herein do not constitute a warranty and are for reference only.

Form No. A95GL1019 Page 1 of 1