

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name : Steel Epoxy Stick, Putty, 50ml
Container size : 50g, 114g

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Two-component, epoxy-based adhesive.

1.3. Details of the supplier of the safety data sheet

Premier Farnell
150 Armley Road
Leeds LS12 2QQ
Tel. : +44 (0) 8701 202530

Emergency telephone number

+44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards : Not Classified
Health hazards : Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 Skin Sens. 1 - H317
Environmental hazards : Aquatic Chronic 2 - H411

2.2. Label elements

Pictogram : 

Signal word : Warning

Hazard statements : H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H412 Harmful to aquatic life with long lasting effects.

Precautionary statements : P261 Avoid breathing vapour/ spray.
P264 Wash contaminated skin thoroughly after handling.
P272 Contaminated work clothing should not be allowed out of the workplace.
P273 Avoid release to the environment.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P302+P352 IF ON SKIN: Wash with plenty of water.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes.
Remove contact lenses, if present and easy to do. Continue rinsing.
P321 Specific treatment (see medical advice on this label).
P332+P313 If skin irritation occurs: Get medical advice/ attention.
P333+P313 If skin irritation or rash occurs: Get medical advice/ attention.
P337+P313 If eye irritation persists: Get medical advice/ attention.
P362+P364 Take off contaminated clothing and wash it before reuse.
P501 Dispose of contents/ container in accordance with national regulations.

Contains : Reaction product: bisphenol-A-(epichlorhydrin)

2.3. Other hazards

NA

SECTION 3: Composition/information on ingredients

3.1. Substances

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

Not applicable

3.2. Mixtures

Talc (Mg₃H₂(SiO₃)₄) 30-60%

CAS number: 14807-96-6

Classification

Not Classified

reaction product: bisphenol-A-(epichlorhydrin) 10-30%

CAS number: 25068-38-6

EC number: 500-033-5

Classification

Skin Irrit. 2 - H315

Eye Irrit. 2 - H319

Skin Sens. 1 - H317

Aquatic Chronic 2 - H411

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

- Inhalation : Remove person to fresh air and keep comfortable for breathing. For breathing difficulties, oxygen may be necessary.
- Ingestion : Rinse mouth thoroughly with water. Do not induce vomiting. Avoid vomiting and stomach flushing because of the risk of aspiration.
- Skin contact : Wash skin thoroughly with soap and water. Remove contaminated clothing. Continue to rinse for at least 10 minutes. Get medical attention.
- Eye contact : Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes. Get medical attention.
- Protection of first aiders : It may be dangerous for first aid personnel to carry out mouth-to-mouth resuscitation.

4.2. Most important symptoms and effects, both acute and delayed

- Ingestion : Irritating to mouth, throat and stomach
- Skin contact : Causes skin irritation. May cause an allergic skin reaction. Redness.
- Eye contact : Causes eye irritation. Pain or irritation. Profuse watering of the eyes. Redness.

4.3. Indication of any immediate medical attention and special treatment needed

- Notes for the doctor : Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

- Suitable extinguishing media : Use fire-extinguishing media suitable for the surrounding fire.
- Unsuitable extinguishing media : None known.

5.2. Special hazards arising from the substance or mixture

- Hazardous combustion products : Thermal decomposition or combustion products may include the following substances: Carbon dioxide (CO₂). Carbon monoxide (CO). Oxides of sulphur. Halogenated hydrocarbons. Metal oxide(s).

5.3. Advice for firefighters

- Special protective equipment for firefighters : Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions : No action shall be taken without appropriate training or involving any personal risk. Evacuate area. Keep unnecessary and unprotected personnel away from the spillage. Provide adequate ventilation.

6.2. Environmental precautions

Environmental precautions : Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air). Avoid discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Avoid generation and spreading of dust. Collect and place in suitable waste disposal containers and seal securely.

6.4. Reference to other sections

Reference to other sections : For personal protection, see Section 8. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions : Wear protective clothing as described in Section 8 of this safety data sheet. Do not get in eyes, on skin, or on clothing. Avoid release to the environment.

Advice on general occupational hygiene

: Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions : Store at temperatures not exceeding 35°C. Store in tightly-closed, original container in a dry, cool and well-ventilated place. Protect from sunlight.

7.3. Specific end use(s)

Specific end use(s) : The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

Talc (Mg₃H₂(SiO₃)₄)

Long-term exposure limit (8-hour TWA): WEL 1 mg/m³ respirable dust

WEL = Workplace Exposure Limit

8.2. Exposure controls

Appropriate engineering controls : Good general ventilation should be adequate to control worker exposure to airborne contaminants.

Eye/face protection : Wear eye protection.

Hand protection : To protect hands from chemicals, gloves should comply with European Standard EN374.

Other skin and body protection : Wear apron or protective clothing in case of contact.

Hygiene measures : Wash hands thoroughly after handling. Wash at the end of each work shift and before eating, smoking and using the toilet. Take off immediately all contaminated clothing.

Respiratory protection : Respirator selection must be based on exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	: Solid.
Colour	: Grey. Black. Dark.
Odour	: Sulphur. Pungent. Strong.
Odour threshold	: Not available.
pH	: Not available.
Melting point	: Not available.
Initial boiling point and range	: Not available.
Flash point	: Not applicable.
Evaporation rate	: Not applicable.
Upper/lower flammability or explosive limits	: Not applicable.
Vapour pressure	: Not applicable.
Vapour density	: Not applicable.
Relative density	: 2.25
Solubility(ies)	: Partly with: Methanol. Ether. Acetone.
Partition coefficient	: Not available.
Auto-ignition temperature	: Not available.
Decomposition Temperature	: >150°C
Viscosity	: Not applicable.
Explosive properties	: Not applicable.
Oxidising properties	: Not available.

9.2. Other information

Other information : None.

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity : -No test data specifically related to reactivity available for this product or its ingredients.

10.2. Chemical stability

Stability : Stable at normal ambient temperatures and when used as recommended.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions : Under normal conditions of storage and use, no hazardous reactions will occur.

10.4. Conditions to avoid

Conditions to avoid : Not known.

10.5. Incompatible materials

Materials to avoid : None known.

10.6. Hazardous decomposition products

Hazardous decomposition products : Does not decompose when used and stored as recommended. No known hazardous decomposition products.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Skin contact : Causes skin irritation. May cause an allergic skin reaction.

Eye contact : Causes serious eye irritation.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity

Toxicity : No data available.

12.2. Persistence and degradability

Persistence and degradability : There are no data on the degradability of this product..

12.3. Bioaccumulative potential

Bioaccumulative potential : Low

Partition coefficient : Not available.

12.4. Mobility in soil

Mobility : Not available

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment : This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects : Not applicable.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information : Dispose of waste product or used containers in accordance with local regulations

Disposal methods : Dispose of waste product or used containers in accordance with local regulations

Waste class : 08 04 09 waste adhesives and sealants containing organic solvents or other dangerous substances.

SECTION 14: Transport information

General : The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation : Regulation (EC) No 1907/2006 of the European Parliament and of the council of 18 December 2006 concerning the Registration, evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC, including amendments. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labeling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Hazard statements in full : H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

Part Number

MP-SES01-50

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.