


COAXIAL CONNECTOR, 7/16, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_716-50-0-3/003_-

Properties

- Rugged connection for COM-Applications
- For medium and high power connection
- Applicable in frequencies up to 7.5 GHz
- IEC Standardized



Product configuration		
Interface type	Gender	Standard
7/16	jack	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data		
Piece parts	Material	Plating
Centre contact	Bronze / Brass	Silver Plating
Outer conductor	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz

Mechanical data	
Weight	0.0816 kg
Mating cycles	500
Flange type	square flange / 32 X 32
Tab style	others

Environmental data	
Operation temperature	-65 °C ... 165 °C

Ordering Information Table		
Item number	Item description	Packaging type
22544104	23_716-50-0-3/003_-E	Single

COAXIAL CONNECTOR, 7/16, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_716-50-0-3/003_-

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2753 / Date of publication: 04.11.2024 / uncontrolled copy