

Borescope



RoHS
Compliant



Features

- Real-time clear display
- Rotatable images
- 2.4 inches TFT screen
- 1m Camera probe
- IP67 Water proof probe
- Battery power indicator

Basic Functions

Pixels	: 640 × 480
Lens Diameter	: 9mm (Max. 10mm)
LCD Size	: 2.4 inches
Probe Length	: 1m
Screen Type	: TFT

Special Functions

Light Source	: 4 LED Lights
Focal Length	: 20mm ~ 100mm
Waterproof	: IP67
Video Signal	: Analogue
Field of View	: 60°
Image Brightness	: 6 Levels-Adjustable
Illumination	: 4 Levels-Adjustable

General Characteristics

Power	: 1.5V AA × 4
LCD Size	: 32mm × 26mm
Colour	: Orange & Grey
Size	: 196mm × 74mm × 38mm

Accessories	Qty.	Note
Operating Manual	1 piece	-
Battery	4 pieces	1.5V AAA × 4, Replaceable

Part Number Table

Description	Part Number
Borescope, 640 × 480 Pixel, 2.4 inches TFT screen, 1m Camera Probe	72-14515

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

