

## Technical data sheet

Article number:  
111-03083

**T30R**



<b>Product Group</b>	Cable Ties inside serrated
<b>Material</b>	Polyamide 6.6 recycled, high impact modified, heat stabilised (PA66HIRHS(REC100))
<b>Colour</b>	Black (BK)
<b>Application Tool</b>	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7ISP
<b>Bundle Diameter max (metric)</b>	35.0 mm
<b>Bundle Ø min.</b>	1.5 mm
<b>Length (L)</b>	150 mm
<b>Min.Tensile Strength</b>	135 N
<b>Package Content packed in</b>	bag
<b>Pack Cont.</b>	100 Bag
<b>Releasable Closure (Yes/No)</b>	No
<b>Thickness (T)</b>	1.1 mm
<b>Toothing (Serration)</b>	Inside Serrated
<b>Variant</b>	Inside Serrated
<b>Width (W)</b>	3.5 mm

**RoHS** ✓