

Technical data sheet

Article number:
111-05018

T50R



Product Group	Cable Ties inside serrated
Material	Polyamide 6.6 recycled, high impact modified, heat stabilised (PA66HIRHS(REC100))
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Diameter max (metric)	50.0 mm
Bundle Ø min.	1.5 mm
Length (L)	200 mm
Min.Tensile Strength	225 N
Pack Cont.	100 Bag
Releasable Closure (Yes/No)	No
Thickness (T)	1.2 mm
Toothing (Serration)	Inside Serrated
Variant	Inside Serrated
Width (W)	4.6 mm

