

Technical data sheet

Article number:
111-00447

T120R



Product Group	Cable Ties inside serrated
Material	Polyamide 6.6 recycled, high impact modified, heat stabilised (PA66HIRHS(REC100))
Colour	Black (BK)
Application Tool	ProCut 9 no battery, EVOcut, MK9P, MK9P w/ Upper air, MK10-SB, MK21, EVO9, EVO9SP, EVO9HT, EVO9i, EVO9iSP, EVO9iHT
Bundle Diameter max (metric)	105.0 mm
Bundle Ø min.	5.0 mm
Height (H)	7.35 mm
Length (L)	387.0 mm
Min.Tensile Strength	535 N
Pack Cont.	100 Bag
Releasable Closure (Yes/No)	No
Thickness (T)	1.9 mm
Toothing (Serration)	Inside Serrated
Variant	Inside Serrated
Width (W)	7.6 mm

