

COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology, NEMP tested

3400.31.0024

Properties

- Ready for TETRA, sub-500 MHz communications and 3GPP band 71
- NEMP tested
- Maintenance-free products
- Highest current handling capability up to 100 kA max.
- Best PIM performance



Product configuration

Main path connectors	Port 1: unprotected, 4.3-10 jack (female) Port 2: protected, 4.3-10 jack (female)
Mounting and grounding	MH110 (bulkhead mounting), M8 (screw), brk (bracket)
Side of bulkhead	protected side
EMP can be install reversed	YES

Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Bronze / Silver Plating Port 2: Bronze / Silver Plating

Electrical data

Impedance	50 Ω
Frequency frame	380 MHz to 700 MHz
Return loss typical	≥ 18 dB
Insertion loss typical	≤ 0.1 dB
CW power frame	≤ 2500 W
Peak power frame	≤ 25 kW
PIM 3rd order	-150 dBc
Residual pulse energy (typ.)	5 μJ LEMP (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs) 520 μJ NEMP (test pulse 10 kV 2.3/23 ns)
Residual pulse voltage (typ.)	11 V LEMP (test pulse 4 kV 1.2/50 ns; 2 kA 8/20 μs) 2650 V NEMP (test pulse 10 kV 2.3/23 ns)
Surge current handling capability	100 kA single, 80 kA multiple (test pulse 8/20 μs)

Electrical bands

	Band 1	Band 2
Frequency range	380 MHz ... 470 MHz	600 MHz ... 700 MHz

COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology, NEMP tested

3400.31.0024

Electrical bands		
	Band 1	Band 2
Return loss typical	≥ 20 dB	≥ 21 dB

Electrical remarks	
Gas tube	No DC / shorted QW or LC

Mechanical data	
Weight	569 g
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP67, according to IEC 60529 (30 min of water, 1 m)
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. A
Moisture resistance according	MIL-STD-202, Method 106

Ordering Information Table	
Item number	Item description
85218128	3400.31.0024

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P43712 / Date of publication: 19.09.2024 / uncontrolled copy