

RoHS
Compliant



Features

- $V_{DS(V)} = 20V$
- $I_D = -2.4A$ ($V_{GS} = 4.5V$)
- $R_{DS(ON)} < 52m\Omega$ ($V_{GS} = 4.5V$)
- $R_{DS(ON)} < 70m\Omega$ ($V_{GS} = 2.5V$)
- $R_{DS(ON)} < 100m\Omega$ ($V_{GS} = 1.8V$)

Absolute Maximum Ratings ($T_a = 25^\circ C$)

Parameter	Symbol	Rating	Unit	
Drain-Source Voltage	V_{DS}	-20	V	
Gate-Source Voltage	V_{GS}	+8		
Continuous Drain Current (Note.1)	I_D	-2.4	A	
Pulsed Drain Current	I_{DM}	-10		
Power Dissipation	P_D	(Note.1)	0.5	W
		(Note.2)	0.46	
Thermal Resistance.Junction- to-Ambient (Note.1)	R_{thJA}	250	$^\circ C/W$	
Thermal Resistance.Junction- to-Case	R_{thJC}	75		
Junction Temperature	T_J	150	$^\circ C$	
Storage Temperature Range	T_{stg}	-55 to 150		

Note.1: $250^\circ C/W$ when mounted on a 0.0^2 in pad of 2 oz. copper.

Note.2: $270^\circ C/W$ when mounted on a minimum pad.

Electrical Characteristics $T_a = 25^\circ C$

Characteristic	Symbol	Conditions	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	V_{DSS}	$I_D = -250\mu A, V_{GS} = 0V$	-20			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = -16V, V_{GS} = 0V$			-1	μA
Gate-Body leakage current	I_{GSS}	$V_{DS} = 0V, V_{GS} = \pm 8V$			± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\mu A$ (Note.1)	-0.4		-1.5	V
Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS} = 2.5V, I_D = 2.4A$ (Note.1)			52	m Ω
		$V_{GS} = -1.8V, I_D = -1.8A$ (Note.1)			70	
		$V_{GS} = 2.5V, I_D = 2.4A$ (Note.1)			100	
On state drain current	$I_{D(ON)}$	$V_{GS} = -4.5V, V_{DS} = -5V$	-10			A
Forward Transconductance	g_{FS}	$V_{DS} = 5V, I_D = -1.25A$		12		S

Characteristic	Symbol	Conditions	Min	Typ	Max	Unit
Input Capacitance	C_{iss}	$V_{GS}=0V, V_{DS}=-10V, f=1MHz$		1312		pF
Output Capacitance	C_{oss}			240		
Reverse Transfer Capacitance	C_{rss}			106		
Total Gate Charge	Q_g	$V_{GS}=-4.5V, V_{DS}=-30V, I_D=-2.4A$		12	20	nC
Gate Source Charge	Q_{gs}			2		
Gate Drain Charge	Q_{gd}			2		
Turn-On Delay Time	$t_{d(on)}$	$V_{GS}=-4.5V, V_{DS}=-10V, I_D=-1A$ $R_G=6\Omega$		15	27	nS
Turn-On Rise Time	t_r			15	27	
Turn-Off Delay Time	$t_{d(off)}$			40	64	
Turn-Off Fall Time	t_f			25	40	
Maximum Body-Diode Continuous Current	I_S				-0.42	A
Diode Forward Voltage	V_{SD}	$I_S=-0.42A, V_{GS}=0V$			-1.2	V

Note: Pulse Test : Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$

Typical Characteristics




Figure 1. On-Region Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 3. On-Resistance Variation with Temperature.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.




Figure 5. Transfer Characteristics.




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics




Figure 7. Gate Charge Characteristics.




Figure 8. Capacitance Characteristics.




Figure 9. Maximum Safe Operating Area.




Figure 10. Single Pulse Maximum Power Dissipation.






Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1b. Transient thermal response will change depending on the circuit board design.

Diagram



Dimensions : Millimetres



Part Number Table

Description	Part Number
P Channel MOSFET, 2.4A, 30V	FDN304P

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.