


RoHS
Compliant



Features

- $V_{DS(V)} = 100V$
- $I_D = -6.6A$ ($V_{GS} = \pm 20V$)
- $R_{DS(ON)} < 28m\Omega$ ($V_{GS} = 10V$)
- $R_{DS(ON)} < 38m\Omega$ ($V_{GS} = 4.5V$)

Absolute Maximum Ratings ($T_a = 25^\circ C$)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DS}	100	V
Gate-Source Voltage	V_{GS}	± 20	
Continuous Drain Current	I_D	6.6	A
Pulsed Drain Current		40	
Power Dissipation ^{1a}	P_D	2.2	W
Power Dissipation ^{1b}		1	
Single Pulse Avalanche Energy ³	E_{AS}	84	mJ
Thermal Resistance.Junction- to-Ambient ^{1a}	R_{thJA}	55	$^\circ C/W$
Thermal Resistance.Junction- to-Case ¹	R_{thJC}	12	
Junction Temperature	T_J	150	$^\circ C$
Storage Temperature Range	T_{stg}	-55 to +150	

Electrical Characteristics $T_a = 25^\circ C$

Characteristic	Symbol	Conditions	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	V_{DSS}	$I_D = -250\mu A, V_{GS} = 0V$	100			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 80V, V_{GS} = 0V$			-1	μA
Gate-Body leakage current	I_{GSS}	$V_{DS} = 0V, V_{GS} = \pm 20V$			± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	1		3	V
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 6.6A$			28	m Ω
		$V_{GS} = 4.5V, I_D = 5.5A$			38	
		$V_{GS} = 10V, I_D = 6.6A, T_J = 125^\circ C$			46	
Forward Transconductance	g_{FS}	$V_{DS} = 5V, I_D = 6.6A$		26		S
Input Capacitance	C_{iss}	$V_{GS} = 0V, V_{DS} = 50V, f = 1MHz$			1490	pF
Output Capacitance	C_{oss}				245	
Reverse Transfer Capacitance	C_{rss}				15	

Characteristic	Symbol	Conditions	Min	Typ	Max	Unit
Gate Resistance	R_g			0.5		Ω
Total Gate Charge	$Q_{g(TOT)}$	$V_{GS}=0V$ to 10V			25	nC
		$V_{GS}=0V$ to 4.5V			12	
Gate Source Charge	Q_{gs}	$V_{DS}=50V, I_D=6.6A$		2.6		nC
Gate Drain Charge	Q_{gd}			2.2		
Turn-On Delay Time	$t_{d(on)}$	$V_{GS}=10V, V_{DS}=50V, I_D=6.6A, R_{GEN}=6\Omega$			14	nS
Turn-On Rise Time	t_r				10	
Turn-Off Delay Time	$t_{d(off)}$				31	
Turn-Off Fall Time	t_f				10	
Body Diode Reverse Recovery Time	t_{rr}	$I_F=6.6A, dI/dt=100A/\mu s$			64	
Body Diode Reverse Recovery Charge	Q_{rr}				58	
Maximum Body-Diode Continuous Current	I_S				6.6	A
Diode Forward Voltage ²	V_{SD}	$I_S=6.6A, V_{GS}=0V$			1.3	V
		$I_S=1A, V_{GS}=0V$			1.2	

NOTES:

1. $R_{\theta JA}$ is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 × 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.

a: 55°C/W when mounted on a 1 in² pad of 2 oz copper

b: 118°C/W when mounted on a minimum pad of 2 oz copper

2. Pulse Test: Pulse Width < 300μs, Duty cycle < 2.0 %.

3. Starting $T_J = 25^\circ C$, L = 1mH, $I_{AS} = 13A$, $V_{DD} = 90V$, $V_{GS} = 10V$.

Typical Characteristics




Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs Case Temperature




Figure 11. Gate Leakage Current vs Gate to Source Voltage




Figure 12. Forward Bias Safe Operating Area

Typical Characteristics




Figure 13. Single Pulse Maximum Power Dissipation





Figure 14. Junction-to-Ambient Transient Thermal Response Curve

Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
N Channel MOSFET, 6.6A, 100V	FDT86102LZ

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.