

ix Type B OM 10xAWG26 PUR 3.0m



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 33 48 323 2A21 030 |
| Specification | ix Type B OM 10xAWG26 PUR 3.0m |
| HARTING eCatalogue | https://b2b.harting.com/33483232A21030 |

Identification

| | |
|---------------|--------------------------------------|
| Category | System cabling |
| Series | HARTING ix Industrial® |
| Element | Cable assemblies |
| Specification | Pre-assembled on both sides |
| Connector 1 | HARTING ix Industrial® PushPull IP20 |
| | Type B |
| | Overmoulded IDC termination |
| Connector 2 | HARTING ix Industrial® PushPull IP20 |
| | Type B |
| | Overmoulded IDC termination |
| Type of cable | Copper cable (round) |

Version

| | |
|--------------------|--------------|
| Cable length | 3 m |
| Number of cores | 10 |
| Core structure | 5x 2x AWG 26 |
| Number of contacts | 10 |

Technical characteristics

| | |
|---------------|---------|
| Rated current | 1.5 A |
| Rated voltage | 50 V AC |
| | 60 V DC |



Pushing Performance
Since 1945

Technical characteristics

| | |
|----------------------|------------------------|
| Limiting temperature | -40 ... +80 °C unmoved |
| | -5 ... +80 °C moved |

Material properties

| | |
|--------------------------------------|--------------------|
| Material (cable) | PUR (polyurethane) |
| Colour (cable) | Grey |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|----------------|-----------------|
| Specifications | EN 50363-10-2 |
| | IEC 61076-3-124 |

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 1 |
| Country of origin | Latvia |
| European customs tariff number | 85444290 |
| GTIN | 5713140333253 |
| eCl@ss | 27060311 Assembled sensor actuator-line |