

## UICIT\_WMRF 8/16\_DUMMY KIT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 024 1033
Specification	UICIT_WMRF 8/16_DUMMY KIT
HARTING eCatalogue	<a href="https://b2b.harting.com/09580241033">https://b2b.harting.com/09580241033</a>

### Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC IT
Element	Connector sets
Specification	Dummy kit

### Version

Gender	Female
--------	--------

### Technical characteristics

Conductor cross-section	1 mm <sup>2</sup> Signal
Conductor cross-section [AWG]	Data AWG 18 Signal
Insulation resistance	>10 <sup>7</sup> Ω
Tightening torque	5 Nm Fixing screws M6
Limiting temperature	-40 ... +90 °C
Mating cycles	≥10,000
Degree of protection acc. to IEC 60529	IP67 / IP69

### Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (hood/housing)	Aluminium die-cast Corrosion resistant



**Pushing Performance**  
Since 1945

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 1003 (signal yellow)
Material (seal)	Silicone
Material (locking)	Stainless steel
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

## Commercial data

Packaging size	1
Net weight	0.661 kg
Country of origin	India
European customs tariff number	85366990
GTIN	5713140492172
ETIM	EC002635
eCl@ss	27440115 Circular connector (set)