



Learn more about
this product



Your Gateway to Efficient Connectivity

Adapter cable with a D-SUB 9 socket connector at one end and an OBD-II (J1962) Type B connector for 24V operation at the other. The OBD-II connector provides access to the on-board diagnostic port, typically located below the steering wheel in cars, and is also used in some trucks and buses. This halogen-free, flame-retardant CAN-bus cable is designed to connect a Kvaser CAN interface or data logger for collecting CAN/OBD-II data.

-  **Warranty**
2-Year warranty. See our general conditions and policies for details.
-  **Support**
Free support for all products by contacting support@kvaser.com
-  **EAN**
73-30130-01407-7

Kvaser OBD-II to D-SUB 9 Adapter Cable 2.5 m

Major Features

- Molded OBD-II (SAE J1962) Type B plug connector that can be connected to both OBD-II receptacle Type B and Type A.
- Molded 9 pin D-SUB socket connector with thumbscrews.
- 2500 mm (approx. 8 ft) long cable made of durable thermoplastic rubber.
- Perfect for Kvaser Memorator, Kvaser Leaf Professional, etc.
- Compatible with J1939, CANopen, NMEA 2000® and DeviceNet. Higher layer protocol translation handled by the user's application. For software support please see our Technical Associates products and our Software Download page (www.kvaser.com).

Support


Documentation, Kvaser SDK and drivers can be downloaded for free at www.kvaser.com/downloads.

Kvaser SDK is a free resource that includes everything you need to develop software for the Kvaser CAN interfaces. Includes full documentation and many program samples, written in C, C++, C#, Delphi, Visual Basic, Python and t script language.

Kvaser CAN hardware is built around the same common software API. Applications developed using one device type will run without modification on other device types.

Technical Data

CAN Channels	1
Certificates	CE, RoHS
Connector	ODB-II Type B D-SUB 9 socket
Length	2500 mm
Material	Thermoplastic polyurethane
Operating Temperature Range	-40 to +85 °C
Strain Relief	Reinforced
Weight	170 g



OBD-II Type B	Signal Name	D-SUB 9
4	GND	3
16	V+	9
6	CAN_H	7
14	CAN_L	2