

- SMT Ring Terminal Probe
- Temperature range -40 to +125°C
- Available in a range of sizes
- Resistance values from 2.2 - 100 kΩ
- Higher temperature range available
- Custom designs available

Applications

Industrial equipment Transit HVAC
Power and utilities Computers Home appliances
Calibration and instrumentation


Specifications

	Unit	Value
Nominal resistance at +25°C	Ohms	10,000
Resistance tolerance from 0..70°C	°C	+/- 0.2
Beta value 25/85	K	3976
Tolerance on Beta value 25/85	%	+/- 0.5
Dissipation constant in still air	mW/°C	2
Operating temperature	°C	-40 to +125
Epoxy thermal conductivity	W/(m.K)	1.7

Materials

Leads and insulation	28AWG Solid silver plated copper leads with white Kynar insulation
Probe material	Tin plated copper

Dimensions in mm





Ordering information

(Please use the characters in the chart below to create your product code)

Sample Code: 93069 ETP - RT - 4 - 24 - 10K3A1B

Probe Size

4	M4
5	M5
6	M6
8	M8
x	optional stud size

Probe cable length

5	50
10	100
15	150
20	200
23	230
25	250
30	300
35	350
40	400
45	450
x	Custom length

Thermistor Type

All thermistor types available: Insert details are required

Stock model:
93069-ETP-RT-4-24-10K3A1B
93549-ETP-RT-4-100-10K3A1B
93079 - ETP-RT-6-24-10K3A1B



Resistance v. temperature table for 10K3A1B Thermistor

Temp. °C	Ohms
-40	336,052
-39	314,512
-38	294,487
-37	275,863
-36	258,533
-35	242,399
-34	227,373
-33	213,371
-32	200,318
-31	188,144
-30	176,786
-29	166,183
-28	156,280
-27	147,029
-26	138,382
-25	130,296
-24	122,732
-23	115,653
-22	109,025
-21	102,817
-20	97,000
-19	91,547
-18	86,433
-17	81,636
-16	77,134
-15	72,907
-14	68,937
-13	65,206
-12	61,700
-11	58,403
-10	55,301
-9	52,383
-8	49,636
-7	47,049
-6	44,612
-5	42,315
-4	40,150
-3	38,109
-2	36,183
-1	34,366
0	32650
1	31,030
2	29,500

Temp. °C	Ohms
3	28,054
4	26,687
5	25,395
6	24,172
7	23,016
8	21,921
9	20,884
10	19,903
11	18,973
12	18,092
13	17,257
14	16,465
15	15,714
16	15,001
17	14,324
18	13,682
19	13,073
20	12,493
21	11,943
22	11,420
23	10,923
24	10,450
25	10,000
26	9,572.0
27	9,164.7
28	8,777.0
29	8,407.8
30	8,056.1
31	7,721.0
32	7,401.7
33	7,097.3
34	6,807.1
35	6,530.3
36	6,266.3
37	6,014.3
38	5,773.8
39	5,544.3
40	5,325.0
41	5,115.7
42	4,915.6
43	4,724.5
44	4,541.7
45	4,367.1

Temp. °C	Ohms
46	4,200.0
47	4,040.2
48	3,887.4
49	3,741.1
50	3,601.1
51	3,467.1
52	3,338.7
53	3,215.8
54	3,098.0
55	2,985.2
56	2,877.0
57	2,773.3
58	2,673.9
59	2,578.6
60	2,487.1
61	2,399.4
62	2,315.2
63	2,234.4
64	2,156.8
65	2,082.3
66	2,010.8
67	1,942.1
68	1,876.0
69	1,812.6
70	1,751.6
71	1,693.0
72	1,636.6
73	1,582.4
74	1,530.2
75	1,480.1
76	1,431.8
77	1,385.3
78	1,340.6
79	1,297.5
80	1,256.1
81	1,216.1
82	1,177.7
83	1,140.6
84	1,104.9
85	1,070.4
86	1,037.3
87	1,005.3
88	974.4

Temp. °C	Ohms
89	944.7
90	916.0
91	888.3
92	861.5
93	835.7
94	810.8
95	786.8
96	763.6
97	741.2
98	719.5
99	698.6
100	678.4
101	658.9
102	640.0
103	621.8
104	604.1
105	587.1
106	570.6
107	554.6
108	539.2
109	524.3
110	509.8
111	495.8
112	482.3
113	469.2
114	456.5
115	444.2
116	432.3
117	420.8
118	409.6
119	398.8
120	388.3
121	378.2
122	368.3
123	358.8
124	349.5
125	340.6