


P/N: 905-120-5000

Description: SMA, Standard Adapter (Coupler)



Amphenol Fiber Optic Products was the pioneer in developing the first industry standard fiber optic interconnect system by introducing the SMA connector & adapter. The 905 Series was the first fiber optic interconnect system to gain industry wide acceptance.

Overview

The Standard SMA Adapter, comes with Dust Caps, Lock Washer and Panel nut. The SMA adapters can be used with single and multi-mode fibers. The SMA adapter is an ideal way to extend cable length by joining two fiber optic cables together. The SMA Adapter has (2) counter-bores on the entry of the adapter, that allows O-ring compatible connectors to inter-connect. This O-ring will protect the connectors from dust and debris.



Features & Benefits

- Quality construction ensures long life, durability & dependability
- Bulkhead Feed-through type, D-Hole mounting
- Dust Caps protect against debris and contamination



Applications

- Medical / Surgical
- Laser Systems
- Industrial
- Spectrometers
- Data Communications

Technical Specifications

Adapter Side A	Threaded 1/4 x 36 2B UNS
Adapter Side B	Threaded 1/4 x 36 2B UNS
Fiber Type	Multi-Mode
Adapter Counterbores	Supports 906 connectors with O-ring compatibility
Weight	.0083 Kg / .018 lbs

Physical Characteristics

SMA Adapter Body	Nickel Plated Brass
Nut	Nickel Plated Brass
Lockwasher	Stainless Steel
Dust Cap	Vinyl
Mounting Hole Recommendation	.281" x .125"
Length	23.50 mm / .925"

Environmental Specifications

Operating Temperature:	-40°C to 85°C
Storage Temperature:	-40°C to 70°C



Contact US


Amphenol Fiber Optic Products
Sales Administration for Quotes,
Orders, and Order Status

1431 Opus Place
Suite 500
Downers Grove, IL 60515

✉ Sales@amphenol-fop.com
☎ 833-499-2385

Revision Date: 2/9/2025
Page : 1

Assembly Drawing



Ordering Information

Order Code:	Customization Options:	MOQ (Minimum Order Quantity):
905-120-5000-P	Individual Packaging Bulk Packaging (100)	300 Pieces

Environmental Specifications

Testing Method:	100% tested for optical performance
-----------------	-------------------------------------

Compliance and Certifications

IEC 61754-22 Compliant:	RoHS / Reach
-------------------------	--------------



Contact US

Amphenol Fiber Optic Products
Sales Administration for Quotes,
Orders, and Order Status

1431 Opus Place
Suite 500
Downers Grove, IL 60515

✉ Sales@amphenol-fop.com
☎ 833-499-2385

Revision Date: 2/9/2025
Page : 2