

Han D-Sub module, Profibus T function




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 009 3151
Specification	Han D-Sub module, Profibus T function
HARTING eCatalogue	https://b2b.harting.com/09140093151

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® D-Sub module
Size of the module	Single module

Version

Termination method	Screw termination
Gender	Female
Number of contacts	9
Details	for RS 485-based bus systems with T-functionality

Technical characteristics

Conductor cross-section	0.08 ... 0.52 mm ²
Rated current	5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (insert)	Polycarbonate (PC) Zinc die-cast
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	34 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140020825
ETIM	EC000438
eCl@ss	27440218 Module for industrial connectors (data)