

4 Channel Programmable Linear Power Supplies

multicomp PRO

RoHS
Compliant



Description

These four-channel DC power supplies can provide pure linear output of 4 isolated channels with features such as stability, free interference, low ripple and low noise. And the power supplies have four-channel cooperative output characteristics, which can realize multi-channel various sequence wave output and complete complex test requirements. Moreover, the output voltage and current can be observed through the oscilloscope of the LCD, and the test data can be directly imported and exported through the U disk.

Features

- 4-channel independent output
- 4-channel high-speed coordinated output, and each channel can be individually controlled with 4-channel output delays as low as microseconds
- LIST programmable output sequence, 100 consecutive different settings
- LIST mode and normal mode can be switched automatically with One Key
- Oscilloscope function for simultaneous display of four channels of voltage and current
- Oscilloscope screen capture via USB access to U disk
- U disk import and export output table data, and you can edit it by computer EXCEL
- Low chopping and low noise
- High resolution and precision
- Remote measurement function
- Built-in USB/RS232/GPIB/LAN communication interfaces

Specifications

Note: The specifications below are tested under the conditions of temperature 25°C ±5°C and the warm-up for 10 minutes.

Models	MP710508	MP710509
Voltage	0 to 30V × 4	0 to 60V × 4
Current	0 to 5A × 4	0 to 3A × 4
Load Regulation		
Voltage	≤1mv	≤1mv
Current	≤1mA	≤1mA
Line Regulation		
Voltage	≤0.01%+1mv	≤0.01%+1mv
Current	≤0.1%+1mA	≤0.1%+1mA

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

4 Channel Programmable Linear Power Supplies

multicomp PRO

Setup Resolution		
Voltage	1mV	1mV
Current	0.1mA	0.1mA
Read Back Resolution		
Voltage	1mV	1mV
Current	0.1mA	0.1mA
Setup Accuracy (25°C ±5°C)		
Voltage	≤0.005% +2mV	≤0.005% +2mV
Current	≤0.05% +1mA	≤0.05% +1mA
Ripple(20-20M)		
Voltage	≤1mVrms	≤1mVrms
Current	≤3mArms	≤3mArms
Temp. Coefficient		
Voltage	≤100ppm	≤100ppm
Current	≤100ppm	≤100ppm
Read Back Temp. Coefficient		
Voltage	≤100ppm	≤100ppm
Current	≤100ppm	≤100ppm
Weight and Dimension	430mm(W) × 88mm(H) × 440mm(D), 16.5Kg	
Input Supply Voltage	115V/230V, 50Hz/60Hz	
Standard Warranty	03 years	
Accessories	User manual	
	Power cord	UK plug + EU plug, Diameter: 0.75mm ² × 3, length: 1.2m
	USB cable	USB cable length 1.5m, USB2, AM to BM
	RS232 cable	RS232 cable length 1.5m
	10A test lead	10A test lead diameter 1.5mm ² , length 0.9m, banana connector 4mm, alligator clip 35mm

Part Number Table

Description	Part Number
Programmable Linear Power Supply, 4 Channel, 0V to 30V, 5A	MP710508
Programmable Linear Power Supply, 4 Channel, 0V to 60V, 3A	MP710509

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO