

POWERSTRIP™/25 SYSTEM MPTC, MPSC SERIES

MPTC Mates with:
MPSC
MPSC Mates with:
MPTC

SPECIFICATIONS

For complete specifications see www.samtec.com?MPTC or www.samtec.com?MPSC

Insulator Material: Black LCP

Terminal Material: Copper Alloy

Plating:

Sn or Au over 50µ" (1,27µm) Ni

Current Rating:

Testing Now!

Operating Temp Range:

-55°C to +105°C

RoHS Compliant:

Yes

Processing:

Max Processing Temp:


230°C for 60 seconds, or

260°C for 20 seconds 3x

Lead-Free Solderable:

Yes

STACK HEIGHT



APPLICATION SPECIFIC OPTION

- Asymmetric power pin placement.
- 4, 8, 16, 36 and 48 total signal pins
- Call Samtec.

ALSO AVAILABLE

- Right Angle. See MPTC-RA Series.

Note: Some sizes, styles and options are non-standard, non-returnable.

MPTC	PWR PINS	SIG PINS	PWR PINS	LEAD STYLE	01	PLATING OPTION	V	OTHER OPTION
-01, -02 = Power Pins Per End	-24 = Total Signal Pins	-80 = Total Signal Pins	-01, -02 = Power Pins Per End	-6.30 = (6,30mm) 0.248"		-L = 10µ" (0,25µm) Gold on contact, Matte Tin on tail (Power & Signal)		-LC = Locking Clip
						-T = Matte Tin on contacts and tail (Power), Gold on contact, Matte Tin on tail (Signal)		

POWER PINS/END	A
-01	(59,44) 2.340
-02	(69,44) 2.734



MPSC	PWR PINS	SIG PINS	PWR PINS	LEAD STYLE	01	PLATING OPTION	V	OTHER OPTION
-01, -02 = Power Pins Per End	-24 = Total Signal Pins	-80 = Total Signal Pins	-01, -02 = Power Pins Per End	-7.70 = (7,70mm) .303"		-L = 10µ" (0,25µm) Gold on contact, Matte Tin on tail (Power & Signal)		-LC = Locking Clip
						-T = Matte Tin on contacts and tail (Power), Gold on contact, Matte Tin on tail (Signal)		

POWER PINS/END	A
-01	(59,44) 2.340
-02	(69,44) 2.734

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM