

Electrical data

| | |
|------------------------------|----------------|
| Eff. operating voltage Ue DC | 24 V |
| Operating voltage DC (UB) | 18 V... 30,2 V |
| Current sum US (Sensor) | 1,1 A |
| Number of plug-in positions | 8 |

Inputs / Outputs

| | |
|--------------------------|-------------|
| Number of inputs | 8 |
| Inputs | PNP, Type 2 |
| Configurable in-/outputs | No |

Bus interface / connection

| | |
|-----------------------|-------------|
| Transmission protocol | IO-Link 1.0 |
| Data rate min. | ? |
| Data rate max. | ? |

LED indication / Diagnosis

| | |
|--------------------------|---|
| Indicator sensors supply | ? |
|--------------------------|---|

| | |
|------------------------------|-----|
| Indicator actuators supply | Yes |
| Indicator switching function | Yes |

Mechanical data

| | |
|------------------------------|-----------------------|
| Enclosure Type per IEC 60529 | IP67 (when connected) |
| Surface protection | ? |
| Width | 30,0 mm |
| Operating temperature Ta | -5 °C... 55 °C |
| Storage temperature | -25 °C... 70 °C |
| Mounting type | 2-hole screw mounting |
| Potting material | UL V-0 |

Scope of Supply

- 12x labels
- Short guide
- 4x plugs M8


Mounting Instruction

See short guide




Definitions see general catalog

Subject to change without notice.



IO-Link
 PIN 1: +24V
 PIN 3: 0V
 PIN 4: IO-Link
 PIN 5: Function ground



Input Ports
 PIN 1: +24V, 200mA
 PIN 3: 0V
 PIN 4: Input

000000000000/164725/0000000000