



Field Attachable Connector



- Create an industrial Ethernet cordset in the field using standard crimp tools
- Achieves IEC IP67 rated seal when mated with an RJ-Lnxx receptacle

When wiring a machine or premise for Ethernet connectivity, it is not always possible to know in advance the exact length




between each connection point. The RJ-Lnxx® field attachable connector enables bulk cable to be pulled to the exact required length, and then terminated to the RJ-45 plug using readily available crimp tools. The completed assembly provides the same sealed, robust connector as the RJ-Lnxx overmolded cordset.

Specifications

| | |
|------------------------|---------------------------------------|
| O-RING MATERIAL: | VITON |
| INSERT MATERIAL: | ACRYLONITRILE-BUTADIENE-STYRENE (ABS) |
| OVERMOLD MATERIAL: | POLYURETHANE |
| COUPLING NUT MATERIAL: | ACRYLONITRILE-BUTADIENE-STYRENE (ABS) |
| SHELL MATERIAL: | ACRYLONITRILE-BUTADIENE-STYRENE (ABS) |
| THREAD SIZE: | UNC 1" - 14 |
| OPERATING TEMPERATURE: | -20° TO 80° C |
| ENVIRONMENTAL RATING: | IEC IP67 |

CONNECTOR DIMENSIONS



| PART NUMBER | DESCRIPTION |
|-----------------|--|
| ENQAM315 | FIELD ATTACHABLE RJ-45 CONNECTOR (STRANDED CORE PLUG) |
| ENSA M315 | FIELD ATTACHABLE RJ-45 CONNECTOR (SOLID CORE PLUG) |
| EN84-2480-3040M | 1000' (304M) OF SOLID CORE, CAT 5E CABLE |
| EN84-2481-3040M | 1000' (304M) OF PROPLEX™ STRANDED, KEVLAR WRAPPED, CAT 5 CABLE |