

Datasheet

Product – High Temperature Cable Ties

Features & Benefits

- Improved performance in high temperature applications
- 150°C for 10,000 hours
- 135°C continuous working temperature
- Use with HellermannTyton cable tie tooling as per table below
- Can withstand intense heat for very short periods
- Ideal for electronics applications

High Temperature Cable Ties - High Grade Nylon 4.6							
Reference	Overall Length mm	Strap Width mm	Minimum Tensile Strength lbs N		Maximum Cable Diameter mm	Recommended Tensioning Tool	Pack Qty
T18R HR	100	2.5	18	80	22	MK3/MK7	200
T30R HR	148	3.6	30	135	35	MK3/MK7	100
T50R HR	202	4.6	50	225	50	MK3/MK7	100
T50I HR	300	4.8	50	222	81	MK3/MK7	100
T50L HR	390	4.7	50	225	110	MK3/MK7	100
T120R HR	390	7.6	120	535	105	MK6/MK9	100