

Performance you can trust

## Anti Seize Compound

**Copper based anti seize paste for all static fasteners and mechanisms.**

**Anti Seize Compound is an assembly and anti seize lubricant that prevents pick up and seizure even in wet, dirty and corrosive conditions.**

### Features

- Temperature range  $-10^{\circ}\text{C}$  to  $1100^{\circ}\text{C}$
- Prevents pick up and seizure of static threaded fasteners
- Lubricates, protects and eases dismantling
- Effective even in the most aggressive environments
- Insoluble in water
- Ideal for furnaces, exhaust systems, dockside and oil rig applications

### Directions for Use

- Apply as a thin film by brushing or wiping onto a clean dry surface.
- For best results apply to both the male and female parts.

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

## Anti Seize Compound

<b>Appearance</b>	Dark coppery coloured paste
<b>NLGI No. (IP 50)(ASTM D217)</b>	NLGI No. 1/2
<b>Base type</b>	Mineral oil
<b>Thickener</b>	Organically modified clay
<b>Solids</b>	Copper, Graphite, MoS <sup>2</sup>
<b>Solids content</b>	Approximately 37%
<b>Temperature range</b>	-10°C to 1100°C
<b>Water solubility</b>	Insoluble
<b>Approximate coverage</b>	5m <sup>2</sup> /kg
<b>Specifications</b>	
<b>Naval Cat No</b>	0475-541-8659 (6kg)
<b>RAF ref No</b>	34D/301-6210 (85g) 34D/224-6794 (500g)
<b>NATO Stock No</b>	8030-99-301-6210 (85g) 8030-99-224-6794 (500g) 8030-99-541-8659 (6kg)
<b>Storage</b>	Storage temperature should be controlled to between 1 and 40 °C.
<b>Pack Sizes – Part Codes</b>	85g – p/c 14030 500g – p/c 14033 6kg – p/c 14035 18kg – p/c 14038

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E customer-service@rocol.com  
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.