

















723 2822
718 3604

Amp	Volt	Hz	IP Ident. colour + h	Part No.	Wall socket outlets with switch	3 P + N + ' 	IEC/EN 60 309	 	EAN No. 4015609...																														
					with double interlocking, switch 3 pole																																		
																																							
16	400	50/60	6	531 25 16				1	039814																														
	110	50/60	4	531 25 14																																			
	230	50/60	9	531 25 19																																			
32	400	50/60	6	531 25 36				1	039869																														
	110	50/60	4	531 25 34																																			
	230	50/60	9	531 25 39																																			
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>a</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>n</th> <th>v</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>127</td> <td>78</td> <td>4,5</td> <td>166</td> <td>97</td> <td>125</td> <td>185</td> <td>7</td> <td>16</td> </tr> <tr> <td>32 A</td> <td>154</td> <td>94</td> <td>4,5</td> <td>193</td> <td>113</td> <td>148</td> <td>215</td> <td>7</td> <td>21</td> </tr> </tbody> </table>					Ampère	a	b	c	d	e	f	n	v	Pg	16 A	127	78	4,5	166	97	125	185	7	16	32 A	154	94	4,5	193	113	148	215	7	21
Ampère	a	b	c	d	e	f	n	v	Pg																														
16 A	127	78	4,5	166	97	125	185	7	16																														
32 A	154	94	4,5	193	113	148	215	7	21																														
					with double interlocking, switch 3 pole																																		
63	400	50/60	6	531 25 66				1	039913																														
	110	50/60	4	531 25 64																																			
	230	50/60	9	531 25 69																																			
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>a</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>n</th> <th>v</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>63 A</td> <td>245</td> <td>125</td> <td>5,2</td> <td>263</td> <td>143</td> <td>172</td> <td>293</td> <td>7</td> <td>29</td> </tr> </tbody> </table>					Ampère	a	b	c	d	e	f	n	v	Pg	63 A	245	125	5,2	263	143	172	293	7	29										
Ampère	a	b	c	d	e	f	n	v	Pg																														
63 A	245	125	5,2	263	143	172	293	7	29																														
					with double interlocking, switch 3 pole																																		
																																							
16	400	50/60	6	531 35 16				1	040124																														
	110	50/60	4	531 35 14																																			
	230	50/60	9	531 35 19																																			
32	400	50/60	6	531 35 36				1	040131																														
	110	50/60	4	531 35 34																																			
	230	50/60	9	531 35 39																																			
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>a</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>n</th> <th>v</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>127</td> <td>78</td> <td>4,5</td> <td>166</td> <td>97</td> <td>132</td> <td>185</td> <td>7</td> <td>16</td> </tr> <tr> <td>32 A</td> <td>154</td> <td>94</td> <td>4,5</td> <td>193</td> <td>113</td> <td>154</td> <td>215</td> <td>7</td> <td>21</td> </tr> </tbody> </table>					Ampère	a	b	c	d	e	f	n	v	Pg	16 A	127	78	4,5	166	97	132	185	7	16	32 A	154	94	4,5	193	113	154	215	7	21
Ampère	a	b	c	d	e	f	n	v	Pg																														
16 A	127	78	4,5	166	97	132	185	7	16																														
32 A	154	94	4,5	193	113	154	215	7	21																														
					with double interlocking, switch 3 pole																																		
63	400	50/60	6	531 35 66				1	040155																														
	110	50/60	4	531 35 64																																			
	230	50/60	9	531 35 69																																			
125	400	50/60	6	531 35 76				1	040186																														
	110	50/60	4	531 35 74																																			
	230	50/60	9	531 35 79																																			
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>a</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>n</th> <th>v</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>63 A</td> <td>245</td> <td>125</td> <td>5,2</td> <td>265</td> <td>143</td> <td>180</td> <td>300</td> <td>7</td> <td>29</td> </tr> <tr> <td>125 A</td> <td>434</td> <td>234</td> <td>11</td> <td>460</td> <td>260</td> <td>263</td> <td>525</td> <td>/</td> <td>42</td> </tr> </tbody> </table>					Ampère	a	b	c	d	e	f	n	v	Pg	63 A	245	125	5,2	265	143	180	300	7	29	125 A	434	234	11	460	260	263	525	/	42
Ampère	a	b	c	d	e	f	n	v	Pg																														
63 A	245	125	5,2	265	143	180	300	7	29																														
125 A	434	234	11	460	260	263	525	/	42																														