



Wiha. Premium Tools
for Professionals.

Wiha 4 mm Reversible Blade Programme. The Flexible System for Precision Mechanics.

4 mm Reversible Blades.



269 Slotted/Slotted Reversible Blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop finish on tip for a perfect fit every time.

Order-No.	⊖	⊖	⊖	⊖	↔	●	▬	
00576 4	0.25 x 1.5	0.5 x 3.0	120	4.0	5			108-671
00577 1	0.4 x 2.0	0.6 x 3.5	120	4.0	5			108-672
00578 8	0.4 x 2.5	0.8 x 4.0	120	4.0	5			108-673



269 Slotted/Phillips Reversible Blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop finish on tip for a perfect fit every time.

Order-No.	⊖	⊖	⊕	↔	●	▬	
00601 3	0.4 x 2.0		PH 00	120	4.0	5	851-607
00602 0	0.5 x 3.0		PH 0	120	4.0	5	108-688
00603 7	0.8 x 4.0		PH 1	120	4.0	5	108-689



269 Phillips/Phillips Reversible Blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop finish on tip for a perfect fit every time.

Order-No.	⊕	⊕	↔	●	▬	
00579 5	PH 000 - PH 00		120	4.0	5	108-674
00580 1	PH 0 - PH 1		120	4.0	5	108-675



269 Pozidriv/Pozidriv Reversible Blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop finish on tip for a perfect fit every time.

Order-No.	⊕	⊕	↔	●	▬	
03186 2	PZ 0 - PZ 1		120	4.0	5	

4 mm Reversible Blades.



269 TORX®/TORX® Reversible Blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop finish on tip for a perfect fit every time.

Order-No.	⊕	⊕	↔	●	▬	
26122 1	T1 - T2		120	4.0	5	
26123 8	T3 - T4		120	4.0	5	
26124 5	T5 - T6		120	4.0	5	
00597 9	T6 - T8		120	4.0	5	108-683
00598 6	T7 - T9		120	4.0	5	108-684
00599 3	T10 - T15		120	4.0	5	108-685
00600 6	T15 - T20		120	4.0	5	108-686



269 Ballpoint Hex/Hex Reversible Blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop finish on tip for a perfect fit every time.

Order-No.	●	●	↔	●	▬	
00582 5	1.3 - 1.3		120	4.0	5	108-677
00583 2	1.5 - 1.5		120	4.0	5	108-678
00584 9	2 - 2		120	4.0	5	108-679
00585 6	2.5 - 2.5		120	4.0	5	108-680
00586 3	3 - 3		120	4.0	5	108-681
00587 0	4 - 4		120	4.0	5	



269 Nut Driver for Hex Nuts.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Order-No.	○	○	↔	●	▬	
00588 7	1.5 - 1.8		120	4.0	5	
00589 4	2 - 2.5		120	4.0	5	



269 Nut Driver for Hex Nuts.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Order-No.	○	↔	●	▬	
00590 0	3	120	4.0	5	
00591 7	3.2	120	4.0	5	
00592 4	3.5	120	4.0	5	
00593 1	4	120	4.0	5	
00594 8	4.5	120	4.0	5	
00595 5	5	120	4.0	5	
00596 2	5.5	120	4.0	5	