


# 3M™ Twisted Pair Flat Cable

.050" 28 AWG Stranded, Mass Terminatable, PVC

1700 Series



- Wires are color-coded for easy identification
- Twist and flat repeat has variable length option
- Can be mass terminated to a broad line of IDC connectors
- Provides reduced crosstalk in balanced drive applications
- 28 AWG stranded wire provides flexibility and extended product life
- 10 color repeat

Date Modified: May 30, 2003

TS-0115-15  
Sheet 1 of 2

---


## Physical

### Insulation

Material: Polyvinyl Chloride (PVC)

Color: 10 Color Repeat with Tan Common

Marking: None

Canadian Option:  AWM 20462 105C 300V VW1 3M NU  AWM IA 80C 150V FT1  
EU <50V

Conductors: 28 AWG 7 x 36 [ 7 x 0.127 ] Tinned Stranded Copper

---

## Electrical

**Voltage Rating:** USA: 300V      Canada: 150V      EU: <50V

**Insulation Resistance:** >1 x 10<sup>9</sup> Ω /10ft [3m]

**Unbalanced**

**Balanced**

**Characteristic Impedance:** 101 Ω

122 Ω

**Capacitance:** 15.9 pF/ft (52.2 pF/m)

13.3 pF/ft (43.6 pF/m)

**Inductance:** 16 μH/ft (0.52 μH/m)

.20 μH/ft (0.66 μH/m)

**Propagation Delay:** 1.61 ns/ft (5.28 ns/m)

1.63 ns/ft (5.35 ns/m)

**Velocity of Propagation:** 63%

62%

Note: Unbalanced is measured between ground-signal-ground conductors. Balanced is measured between conductors within a pair.

---

## Environmental

**Temperature Rating:** USA: -20° C to +105° C      Canada: -20° C to +80° C

**Flammability Rating:** USA: VW-1

Canada: FT1

UL File No.: E42769, Style No.: 20462

**3M**

Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call

800-225-5373


# 3M™ Twisted Pair Flat Cable

## .050" 28 AWG Stranded, Mass Terminatable, PVC


1700 Series




Number of Conductors	3M Part Number	Dimension A	Dimension B
10 (5 pair)	<b>1700/10</b>	0.50 [ 12.7 ]	0.450 ± .010 [ 11.43 ]
14 (7 pair)	<b>1700/14</b>	0.70 [ 17.8 ]	0.650 ± .010 [ 16.51 ]
16 (8 pair)	<b>1700/16</b>	0.80 [ 20.3 ]	0.750 ± .015 [ 19.05 ]
20 (10 pair)	<b>1700/20</b>	1.00 [ 25.4 ]	0.950 ± .015 [ 24.13 ]
26 (13 pair)	<b>1700/26</b>	1.30 [ 33.0 ]	1.250 ± .015 [ 31.75 ]
34 (17 pair)	<b>1700/34</b>	1.70 [ 43.2 ]	1.650 ± .020 [ 41.91 ]
36 (18 pair)	<b>1700/36</b>	1.80 [ 45.7 ]	1.750 ± .020 [ 44.45 ]
40 (20 pair)	<b>1700/40</b>	2.00 [ 50.8 ]	1.950 ± .020 [ 49.53 ]
50 (25 pair)	<b>1700/50</b>	2.50 [ 63.5 ]	2.450 ± .020 [ 62.23 ]
60 (30 pair)	<b>1700/60</b>	3.00 [ 76.2 ]	2.950 ± .020 [ 74.93 ]
64 (32 pair)	<b>1700/64</b>	3.20 [ 81.3 ]	3.150 ± .020 [ 80.01 ]



Variable Length Suffix Table		
Example of alternate twist and flat repeats		
Suffix	Repeat	Flat
<b>TO</b>	22.00	4.00
<b>TB</b>	7.50	1.00
<b>TD</b>	43.00	3.00
<b>BP</b>	9.00	1.50
<b>EA</b>	10.50	2.00
<b>BW</b>	34.00	2.00




- \* 10 Color Repeat
- Brown/Tan
- Red/Tan
- Orange/Tan
- Yellow/Tan
- Green/Tan
- Blue/Tan
- Violet/Tan
- Gray/Tan
- White/Tan
- Black/Tan



Inch [mm]			
Tolerance Unless Noted			
	.0	.00	.000
Inch	±.1	±.01	±.005

[ ] Dimensions for Reference only

### Ordering Information



**Notes:**

- Available in standard lengths of 100 feet or 300 feet per roll, please specify when ordering.
- Standard product has a twist-flat repeat length of 20 inches (50.8 cm), with a 2-inch (5.1 cm) flat portion. The twist-flat repeat can be specified from 8-1/2 inches (16.5 cm) to 48 inches (1.219 m), and the flat can be specified as anything over 1 inch (2.5 cm).
- For special requirements, contact your 3M representative.

TS-0115-15  
Sheet 2 of 2

### **Important Notice**

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



### **Electronic and Interconnect Solutions Division**

6801 River Place Blvd.  
Austin, TX 78726-9000  
[www.3M.com/eisd](http://www.3M.com/eisd)

### **Warranty; Limited Remedy; Limited Liability.**

This product will be free from defects in material and manufacture for a period of 1 year from the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**