




**GR881-H (8K x 8)
NON-VOLATILE RAM**

**GREENWICH
INSTRUMENTS LTD**



TIMING (nS-nano seconds)

Symbol	Parameter	70nS	
		Min	Max
t_{RC}	Read cycle time	70	
t_{ACC}	Access time	70	
t_{ACS}	\overline{CE} to output valid	70	
t_{OE}	\overline{OE} to output valid	35	
t_{CLZ}	\overline{CE} to output active	10	
t_{OLZ}	\overline{OE} to output active	10	
t_{OH}	Output hold time	10	
t_{CHZ}	\overline{CE} to output disable	25	
t_{OHz}	\overline{OE} to output disable	25	



Symbol	Parameter	70nS	
		Min	Max
t_{WC}	Write cycle time	70	
t_{WP}	Write pulse width	50	
t_{AS}	Address setup time	0	
t_{WR}	Write recovery time	0	
t_{WHZ}	\overline{WR} to output disable	20	
t_{OW}	Output active from \overline{WR}	5	
t_{DS}	Data setup time	30	
t_{DH}	Data HOLD TIME	0	

Notes

1. WE must be high during address transitions.
2. A Write occurs during the overlap of active \overline{CE} and a low \overline{WE} .
3. $\overline{CE} = \overline{CE1}$ and $\overline{CE2}$
4. WE is high for a read cycle.




REPLACES 6264., 5565., etc.

DIMENSIONS (mm)



**GR881-H (8K x 8)
NON-VOLATILE RAM**

**GREENWICH
INSTRUMENTS LTD**



TIMING (nS-nano seconds)

Symbol	Parameter	70nS	
		Min	Max
t_{RC}	Read cycle time	70	
t_{ACC}	Access time	70	
t_{ACS}	\overline{CE} to output valid	70	
t_{OE}	\overline{OE} to output valid	35	
t_{CLZ}	\overline{CE} to output active	10	
t_{OLZ}	\overline{OE} to output active	10	
t_{OH}	Output hold time	10	
t_{CHZ}	\overline{CE} to output disable	25	
t_{OHz}	\overline{OE} to output disable	25	



Symbol	Parameter	70nS	
		Min	Max
t_{WC}	Write cycle time	70	
t_{WP}	Write pulse width	50	
t_{AS}	Address setup time	0	
t_{WR}	Write recovery time	0	
t_{WHZ}	\overline{WR} to output disable	20	
t_{OW}	Output active from \overline{WR}	5	
t_{DS}	Data setup time	30	
t_{DH}	Data HOLD TIME	0	

Notes


1. WE must be high during address transitions.
2. A Write occurs during the overlap of active \overline{CE} and a low \overline{WE} .
3. $\overline{CE} = \overline{CE1}$ and $\overline{CE2}$
4. WE is high for a read cycle.

REPLACES 6264., 5565., etc.

DIMENSIONS (mm)



**GR881-H (8K x 8)
NON-VOLATILE RAM**



**GREENWICH
INSTRUMENTS LTD**

ABSOLUTE MAXIMUM RATINGS

Symbol	Min	Max	Units
Vdd	-0.3	7.0	Volts
Vi/o	-0.3	Vdd +0.3	Volts
Temp	-40	+85	deg. C

DESCRIPTION

The GR881-H is an industrial temperature range, 8192 word by 8 bits (8K x 8) non-volatile CMOS Static Ram, fabricated from advanced silicon gate CMOS technology and a high reliability lithium power cell. The pin-out of the GR881-H conforms to the JEDEC standards and is fully compatible with normal static RAM.

The power down circuit is fully automatic and is referenced at 4.5 volts. At this point the GR881-H is write protected by an internal inhibit function for Data Protection and the memory contents are retained by the lithium power source.

Power down is very fast, this being essential for data integrity, taking a maximum of 15 μ s (15 microseconds) to power down from 5 volts to 0 volts. This is much faster than system power failure conditions. Therefore there are no special conditions required when installing the GR881-H.

The GR881-H can, without external power, retain data almost indefinitely. The limiting factor will be the shelf life of the lithium cell, which is typically ten years. It is possible that this figure may be extended in view of the extremely light duty imposed upon the cell.

APPLICATION

When powered down, the GR881-H is transportable and data can be moved from system to system, this makes it ideal for program development, data collection in data loggers, program changes in process control, automation and robotics and user definable lookup tables, etc.

DISPOSAL INSTRUCTIONS

Do not dispose of non-volatile memory devices by incineration or crushing. Devices may be returned carriage paid to Greenwich Instruments Ltd., for disposal.

UK

Greenwich Instruments Ltd.,
Meridian House, Park Road,
Swanley, Kent. BR8 8AH
Tele: 08700 505 404
Fax: 08700 505 405

Greenwich Instruments Ltd., are continually developing their products and reserve the right to alter specifications without prior notice. Standard Terms and Conditions of Sale apply.

OPERATING CONDITIONS

Symbol	Min	Typ	Max	Unit
Vdd	4.75	5.0	5.5	Volts
Vin (1)	2.2		Vdd+0.3	Volts
Vin (0)	-0.3		0.8	Volts
Iin (any other pin)	-1.0		+1.0	μ A
Vout (1)(Iout = -1mA)	2.4			Volts
Vout (0)(Iout = +2mA)			0.4	Volts
Idd (Active)		30		mA
Idd (Deselected)		1.0		mA
Tcycle			70	nS
Cin (any pin)		10		pF


OPERATING MODE

CE	OE	WR	MODE	OUTPUT	Idd
H	X	X	Unsel.	Hi-Z	Standby
L	H	H	Unsel.	Hi-Z	Active
L	L	H	Read	Dout	Active
L	X	L	Write	Din	Active

PIN CONNECTIONS


NC	1	28	Vdd	Pin	Function
A12	2	27	WR	A0-A12	Address I/P's
A7	3	26	CE ₂	A0-A12	Address I/P's
A6	4	25	A8	D0-D7	Data in/out
A5	5	24	A9	D0-D7	Data in/out
A4	6	23	A11	OE	Output Enable
A3	7	22	OE	CE ₁ CE ₂	Chip Enable
A2	8	21	A10	WR	Write Enable
A1	9	20	CE ₁	A10	Write Enable
A0	10	19	Vdd	CE ₁	+5Volt Power
D0	11	18	D6	Vdd	+5Volt Power
D1	12	17	D5	GND	Ground
D2	13	16	D4		
GND	14	15	D3		

DATA RETENTION OPERATING CONDITIONS



Symbol	Parameter	Min	Typ	Max	Units
Vdd	Operating supply voltage	4.75	5.0	5.50	Volts
VTH	Data retention voltage		4.5		Volts
t _F	Vdd slew to 0V		15		μ s
t _R	Vdd slew 0V to 5.0V		15		μ s
t _{REC}	CE to O/P valid from power up			15	μ s
t _{DR}	Data retention time		10		Years
t _{PD}	CE at Vin(1) before power down	0			μ s

**GR881-H (8K x 8)
NON-VOLATILE RAM**



DESCRIPTION

The GR881-H is an industrial temperature range, 8192 word by 8 bits (8K x 8) non-volatile CMOS Static Ram, fabricated from advanced silicon gate CMOS technology and a high reliability lithium power cell. The pin-out of the GR881-H conforms to the JEDEC standards and is fully compatible with normal static RAM.

The power down circuit is fully automatic and is referenced at 4.5 volts. At this point the GR881-H is write protected by an internal inhibit function for Data Protection and the memory contents are retained by the lithium power source.

Power down is very fast, this being essential for data integrity, taking a maximum of 15 μ s (15 microseconds) to power down from 5 volts to 0 volts. This is much faster than system power failure conditions. Therefore there are no special conditions required when installing the GR881-H.

The GR881-H can, without external power, retain data almost indefinitely. The limiting factor will be the shelf life of the lithium cell, which is typically ten years. It is possible that this figure may be extended in view of the extremely light duty imposed upon the cell.

APPLICATION

When powered down, the GR881-H is transportable and data can be moved from system to system, this makes it ideal for program development, data collection in data loggers, program changes in process control, automation and robotics and user definable lookup tables, etc.

DISPOSAL INSTRUCTIONS

Do not dispose of non-volatile memory devices by incineration or crushing. Devices may be returned carriage paid to Greenwich Instruments Ltd., for disposal.

UK

Greenwich Instruments Ltd.,
Meridian House, Park Road,
Swanley, Kent. BR8 8AH
Tele: 08700 505 404
Fax: 08700 505 405

Greenwich Instruments Ltd., are continually developing their products and reserve the right to alter specifications without prior notice. Standard Terms and Conditions of Sale apply.

ABSOLUTE MAXIMUM RATINGS

Symbol	Min	Max	Units
Vdd	-0.3	7.0	Volts
Vi/o	-0.3	Vdd +0.3	Volts
Temp	-40	+85	deg. C

OPERATING CONDITIONS

Symbol	Min	Typ	Max	Unit
Vdd	4.75	5.0	5.5	Volts
Vin (1)	2.2		Vdd+0.3	Volts
Vin (0)	-0.3		0.8	Volts
Iin (any other pin)	-1.0		+1.0	μ A
Vout (1)(Iout = -1mA)	2.4			Volts
Vout (0)(Iout = +2mA)			0.4	Volts
Idd (Active)		30		mA
Idd (Deselected)		1.0		mA
Tcycle			70	nS
Cin (any pin)		10		pF


OPERATING MODE

CE	OE	WR	MODE	OUTPUT	Idd
H	X	X	Unsel.	Hi-Z	Standby
L	H	H	Unsel.	Hi-Z	Active
L	L	H	Read	Dout	Active
L	X	L	Write	Din	Active

PIN CONNECTIONS

NC	1	28	Vdd	Pin	Function
A12	2	27	WR	A0-A12	Address I/P's
A7	3	26	CE ₂	A0-A12	Address I/P's
A6	4	25	A8	D0-D7	Data in/out
A5	5	24	A9	D0-D7	Data in/out
A4	6	23	A11	OE	Output Enable
A3	7	22	OE	CE ₁ CE ₂	Chip Enable
A2	8	21	A10	WR	Write Enable
A1	9	20	CE ₁	A10	Write Enable
A0	10	19	Vdd	CE ₁	+5Volt Power
D0	11	18	D6	Vdd	+5Volt Power
D1	12	17	D5	GND	Ground
D2	13	16	D4		
GND	14	15	D3		

DATA RETENTION OPERATING CONDITIONS



Symbol	Parameter	Min	Typ	Max	Units
Vdd	Operating supply voltage	4.75	5.0	5.50	Volts
VTH	Data retention voltage		4.5		Volts
t _F	Vdd slew to 0V		15		μ s
t _R	Vdd slew 0V to 5.0V		15		μ s
t _{REC}	CE to O/P valid from power up			15	μ s
t _{DR}	Data retention time		10		Years
t _{PD}	CE at Vin(1) before power down	0			μ s