

# SECTION 2 PCB TERMINAL BLOCKS

**PCB  
TERMINAL  
BLOCKS**


## 3.5mm Pitch **Ultra Low Profile** Screw Terminal 3882615 + 3882627

### Features

- Ultra low profile
- Stainless steel wire protector
- 2-12 pole interlocking
- Flame retardant material
- Double interlock mechanism for increased strength
- UL & CSA applied for
- 1mm<sup>2</sup> cable entry
- Anti solder wicking terminals
- Captive screws
- Guided pin alignment
- Standard colour black. Other colours available



Type No.	Poles	Length
CTB3051/2	2	7mm
CTB3051/3	3	10.5mm
CTB3051/4	4	14mm
CTB3051/5	5	17.5mm
CTB3051/6	6	21mm
CTB3051/7	7	24.5mm
CTB3051/8	8	28mm
CTB3051/9	9	31.5mm
CTB3051/10	10	35mm
CTB3051/11	11	38.5mm
CTB3051/12	12	42mm



### Specification

Rating	10A/125Vac
Dielectric strength	1.5kV
Insulation resistance	5MΩ/1000V
Working temperature	-33°C to 125°C
Short period	160°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	5μ tinned, nickel plated copper flash brass
Screw/torque	M2 steel, 5μ zinc & colour passivated 0.4Nm max
Recommended PCB hole size	ø1.1mm


## 3.5mm Pitch **Ultra Low Profile 90°** Screw Terminal

### Features

- Ultra low profile
- Stainless steel wire protector
- 2-12 pole interlocking
- Flame retardant material
- Double interlock mechanism for increased strength
- UL & CSA applied for
- 1mm<sup>2</sup> cable entry
- Anti solder wicking terminals
- Captive screws
- Guided pin alignment
- Standard colour black. Other colours available



Type No.	Poles	Length
CTB3551/2	2	7mm
CTB3551/3	3	10.5mm
CTB3551/4	4	14mm
CTB3551/5	5	17.5mm
CTB3551/6	6	21mm
CTB3551/7	7	24.5mm
CTB3551/8	8	28mm
CTB3551/9	9	31.5mm
CTB3551/10	10	35mm
CTB3551/11	11	38.5mm
CTB3551/12	12	42mm



### Specification

Rating	10A/125Vac
Dielectric strength	1.5kV
Insulation resistance	5MΩ/1000V
Working temperature	-33°C to 125°C
Short period	160°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	5μ tinned, nickel plated copper flash brass
Screw/torque	M2 steel, 5μ zinc & colour passivated 0.4Nm max
Recommended PCB hole size	ø1.1mm



FM28614  
BS EN ISO 9002:  
1994

Tel: +44 (0)1727 864437 Fax: +44 (0)1727 855400  
E-mail: [info@camden-electronics.co.uk](mailto:info@camden-electronics.co.uk) Website: [www.camden-electronics.co.uk](http://www.camden-electronics.co.uk)

Because we operate a constant improvement policy, our products are subject to change without notice.

**CAMDEN**  
ELECTRONICS LTD