

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG	


REVISIONS			DOC. NO	I. SPC-F005	* Effe	ctive: 7/8/	'02 * DO	CP No: 1398
DCP #	RE∨	DESCRIPTION	DRAWN	DRAWN DATE C		DATE	APPR∨I	DATE
1993	Α	Released		5/27/10	JYC	5/27/10	JYC	5/27/10

MATERIAL

2-1. Frame : Thermoplastic PBT of UL 94V-0

2-2. Impeller : Thermoplastic PBT of UL 94V-0





- 1. One directional exhaust.
- 2. Best Mounting Direction: Fan blade face up or shaft horizontal direction.

Units:mm

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:


UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:
Jerrold Chen	5/27/2010
CHECKED BY:	DATE:
Jerrold Chen	5/27/2010
APPROVED BY:	DATE:
Jerrold Chen	5/27/2010

	DRAW	'ING TITLE:								
10		Brushless DC Motor								
╝	SIZE	DWG. N□.	OWG. NO. ELECTRONIC FILE						RE∨	
10	Α		MC3	MC35356 75R9907					Α	
0	SCAL	SCALE: NTS U, D, M, 1 mm			SHEET:	1	OF	3		

PERFORMANCE CURVES

STATIC PRESSURE



ALL RIGHTS RESERVED NO PORTION OF THIS PUR	ICATION WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT	SIZE	SIZE DWG, ND, ELECTR				E		REV
	RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.		MC	35356		75R9907			Α
SPC-F005.DWG	DDC. ND. SPC-F005 * Effective: 7/8/02 * DCP No: 1398	SCAL	E: NTS	U.□.M.: Millimeters		SHEET:	2	OF 3	3

SPECIFICATIONS

1-1. Rated Voltage : 12 VDC

1-2. Operating Voltage Range : 4.5~13.8 VDC

1-3. Starting Voltage : 4.5 VDC (25 deg. C PDWER DN/DFF)

1-4 Rated Speed : 5500 RPM ± 15% at rated voltage

1-5. Acoustic Noise : 31 dB(A)

1-6. Static Pressure : 0.15 Inch-H20

1-7. Rated Current : 110 mA / Max 127 mA 1-8. Rated Power : 1.32 W / Max 1.52 W

1-9. Weight : 17.5g

1-10. Direction of Rotation : Counter-clockwise viewed from front of fan blade

1-11. Operating Temperature : -10 to +70 deg. C 1-12. Storage Temperature : -40 to +70 deg. C

1-13. Bearing System : VAPO bearing system

1-14. Air Flow : 13.8 CFM

1-14. Locked Rotor Protection : Automatic Restart Capacity

Note: In a situation where the fan is locked by a external force while the electricity is on, an increase in coil

temperature will be prevented by temporarily turning off

the electrical power to the motor. The fan will

automatically restart when the locked rotor condition is

released.

ALL RIGHTS RESERVED, NO PORTION OF THIS PUBLI	CATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT	SIZE	DWG. N□.		ELECT	RONIC FILE	F	₹EV
THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.		A	MC:	35356		75R9907		Α
SPC-F005.DWG	DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398	SCALE	E: NTS	U.□.M.: Millimeters		SHEET: 3	□F 3	3