

3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG

Product Description

3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG is designed to have lower outgassing and lower ionics than 3M™ Scotch-Weld™ Epoxy Adhesive DP-460. Laboratory testing has shown that 3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG's curing and adhesive performance to be comparable to 3M™ Scotch-Weld™ Epoxy Adhesive DP-460.

Application Ideas

- Hard Disk Drive Assembly
- Spindle Motor Assembly
- Magnet Bonding
- E-Block Assembly
- Bearing Cartridge Assembly
- Potting
- Rigidizing

Key Features

- Curing and bonding performance comparable to 3M™ Scotch-Weld™ Epoxy Adhesive DP-460.
- Total outgassing < 1000 $\mu\text{g/g}$ (via GC/MS, 85°C for 3 hours).
- Siloxane outgassing $\leq 5 \mu\text{g/g}$ (via GC/MS, 85°C for 3 hours).
- Lower chloride ion content than standard epoxies.

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product		3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG
Viscosity (at 72°F [23°C])	Base Accelerator Mixed	25,000 - 45,000 cps 8,000 - 14,000 cps 15,000 - 25,000 cps
Base Resin	Base Accelerator	Epoxy Amine
Color	Base Accelerator	White Amber
Net Weight (lb/gallon)	Base Accelerator	9.4 9.0
Mix Ratio (B:A)	Volume Weight	2:1 2:0 : 0.96
Worklife (72°F [23°C])		110 minutes




3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG

Curing

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

This adhesive will cure in 24 hours at room temperature. Heating will accelerate the cure and can result in a higher T_g than room temperature curing yields. Curing data is shown in the figure below.



Note: If the adhesive has become grainy or lumpy in appearance when dispensed, this may be due to crystallization of the adhesive. This can be corrected by heating the adhesive in the syringe to 120°F (49°C) for 30 minutes, then allowing the adhesive to cool before dispensing.

3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG

Typical Performance Characteristics¹

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Shear and Peel Strength vs. Cure Temperature / Time

	72°F (23°C) 24 hours	120°F (49°C) 270 minutes	160°F (71°C) 90 minutes	200°F (93°C) 30 minutes	250°F (121°C) 10 minutes
Overlap Shear² (lbf/in ²) (ASTM D-1002-72)	> 5000	> 5000	> 5500	> 5500	> 5500
T-Peel³ (lbf/in) (ASTM D1876-61T)	60 ⁴	59 ⁴	43 ⁴	39 ⁵	45 ⁵

¹ - See Technical Data Sheet 3M™ Scotch-Weld™ Epoxy Adhesive DP-460 for additional typical performance characteristics.

² - 0.060 inch thick, etched aluminum pulled at 0.10 inches/minute.

³ - 0.032 inch thick, anodized aluminum pulled at 20 inches/minute.

⁴ - Cohesive failure mode.

⁵ - Adhesive failure mode.

Storage and Shelf Life

Storage: Store 3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG at 60-80°F (15-27°C) or refrigerate for maximum shelf life.

Shelf Life: 3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG has a shelf life of 15 months in its original container.

3M™ Scotch-Weld™ Epoxy Adhesive DP-460 EG

Certification/Recognition

MSDS: Refer to Product Label and Material Safety Data Sheet for Health and Safety Information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

RoHs Complaint/REACH Compliant: This product complies with the European Union's "Restriction of Hazardous Substances" (RoHs) initiative and with European REACH regulations 2002/95/EC and 2005/618/EC.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M, Electronics Markets Materials Division, 3M Center, Building 225-3S-06, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Markets Materials Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M and Scotch-Weld are trademarks
of 3M Company.
Please recycle. Printed in U.S.A.
© 3M 2010. All rights reserved.
78-6900-9832-8

