


# Spezifikation für Freigabe / specification for release

Kunde / customer : \_\_\_\_\_  
 Artikelnummer / part number : **7427415** LF  
 Bezeichnung : **CPU Ferrit Platte**  
 description : **CPU ferrite core**



DATUM / DATE : 2004-10-11

## A Mechanische Abmessungen / dimensions:




|   | 23x0,8x23          |    |
|---|--------------------|----|
| A | <b>23,0 ± 0,60</b> | mm |
| B | <b>0,8 ± 0,20</b>  | mm |
| C | <b>23,0 ± 0,60</b> | mm |
| D |                    | mm |
| E |                    | mm |
| F |                    | mm |
| G |                    | mm |
| H |                    | mm |
| I |                    | mm |

## B Elektrische Eigenschaften / electrical properties:

| Eigenschaften / properties                  | Testbedingungen / test conditions |       | Wert / value | Einheit / unit | tol.        |
|---|-----------------------------------|-------|--------------|----------------|-------------|
| Impedanz / impedance                        | <b>25 MHz</b>                     | Z     | <b>24</b>    | Ω              | <b>±25%</b> |
| Impedanz / impedance                        | <b>100 MHz</b>                    | Z     | <b>79</b>    | Ω              | <b>±25%</b> |
| Material / material                         | <b>NiZn</b>                       |       | <b>5W700</b> |                |             |
| Anfangspermeabilität / initial permeability |                                   | μ iac | <b>700</b>   |                |             |
| Curie Temperatur / Curie temperature        |                                   | Tc    | <b>140</b>   | °C             | <b>max.</b> |

## C Lötpad / soldering spec.:



## D Prüfgeräte / test equipment:

**HP 4191 B** für/for Z und/and material  
**HP 16092A** Fixture 0,65 wire 2UEW\*100mm 1/2 Turns

## E Testbedingungen / test conditions:

Luftfeuchtigkeit / humidity: 33%  
 Umgebungstemperatur / temperature: +20°C

## F Werkstoffe & Zulassungen / material & approvals

Basismaterial / base material: Ferrit / ferrite

## G Eigenschaften / general specifications:

Lagertemperatur / storage temperature: -55°C ~ + 125°C  
 Betriebstemp. / operating temperature: -25°C ~ +125°C

|                                     |                          |      |                         |
|-------------------------------------|--------------------------|------|-------------------------|
| Freigabe erteilt / general release: | <b>Kunde / customer</b>  |      |                         |
| .....                               | .....                    |      |                         |
| Datum / date                        | Unterschrift / signature |      |                         |
|                                     | <b>Würth Elektronik</b>  |      |                         |
| .....                               | .....                    |      |                         |
| Geprüft / checked                   | Kontrolliert / approved  | LF   | RoHS update             |
|                                     |                          | Name | Änderung / modification |
|                                     |                          |      | Datum / date            |

### Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400  
<http://www.we-online.com>


# Spezifikation für Freigabe / specification for release

Kunde / customer : \_\_\_\_\_  
 Artikelnummer / part number : **7427415** LF  
 Bezeichnung : **CPU Ferrit Platte**  
 description : **CPU ferrite core**



DATUM / DATE : 2004-10-11

## H Impedanzverlauf / impedance curve:



|                                     |                          |      |                                |              |
|-------------------------------------|--------------------------|------|--------------------------------|--------------|
| Freigabe erteilt / general release: | <b>Kunde / customer</b>  |      |                                |              |
| Datum / date                        | Unterschrift / signature |      |                                |              |
|                                     | <b>Würth Elektronik</b>  |      |                                |              |
| Geprüft / checked                   | Kontrolliert / approved  | LF   | RoHS update                    | 04-10-11     |
|                                     |                          | Name | <b>Änderung / modification</b> | Datum / date |

This electronic component is designed and developed with the intention for use in general electronics equipments. Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body. In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before use. It is essential to give consideration when to install a protective circuit at the design stage.

### Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400  
<http://www.we-online.com>