


NO	DESCRIPTION	DATE
①	REDUCE SPRING FROM 2PCS TO 1 PC	06.06.97
②	BACKGROUND FORMAT UPDATED	07.08.02'
③	BACKGROUND FORMAT UPDATED	11.18.08'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-4 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 WORKING VOLTAGE: 500 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 1000 VOLTS
- 1.5 VSWR: 1.3 MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -20° C TO +80° C

9	CHASSIS	BRASS	1	NICKEL 100μ" MIN.
8	BODY	BRASS	1	NICKEL 100μ" MIN.
7	WASHER	BRASS	1	NICKEL
6	SPRING WASHER	SK-5	1	NICKEL
5	GASKET	RUBBER	1	RED
4	WASHER	BRASS	1	NICKEL
3	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD
2	INSULATION	TEFLON	1	NONE
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by _____ DATE: _____

DESCRIPTION		SMA JACK-BNC PLUG		DATE		REV.	
製圖	DRAWN	TOLERANCE	品名	19-38-1	T.G.N	日期	11.27.95'
檢圖	CHECK	.XX ±0.2	TITLE	\ROHS COMPLIANT (50Ω)		版次	A-3
認圖	APPROVAL	.XXX ±0.05	單位	DWG.NO.	19-0136	佳楠精密電子股份有限公司	
	Lewis	ANGLE ±5°	SCALE	4:1		CHIN NAN PRECISION ELECTRONICS CO.,LTD.	