

MAROON Wireless MultiMedia Desktop M82-24825



Facts & Features

- Limited Edition Wireless MultiMedia keyboard/mouse set in attractive colour combination
- Plug & Play for easy start up with no software installation
- Multiple-use capability: multiple devices can be used in one room
- Wireless freedom with 2.4 GHz wireless technology offering a 10 m range and interruption-free transmission
- 10 hotkeys, with the most common multimedia functions already allocated
- **Optical 5-button mouse**
 - Browser forward / back buttons
 - Precise and rapid scanning of the surface with a maintenance-free optical sensor * with 1000 dpi resolution
- Standard keyboard layout (including cursor and number block)
- Problem-free use of your standard batteries (batteries included in the scope of delivery)

* Optimal performance on non-reflective surfaces only

Delivery volume

- 1 wireless keyboard
- 1 wireless mouse
- 1 receiver
- 4 batteries type AAA
- 1 printed manual

Approvals

- CE, FCC, cURus, c-tick, GOST-R, UL

Operating system

- Microsoft Windows® XP, Vista

System requirements

- USB interface

Technical data

- Number of buttons:
105 + 10 = european layout
- Weight:
approx. 630 g (keyboard)
approx. 120 g (mouse)
approx. 10 g (receiver)
approx. 1200 g (with packaging)
- Dimensions in mm:
approx. 456 x 204 x 25 (keyboard)
approx. 120 x 65 x 40 (mouse)
approx. 41 x 14 x 7 (receiver)
approx. 530 x 252 x 80 (packaging)
- Storage temperature:
-20 °C to 65 °C
- Operating temperature:
0 °C to 50 °C
- Transmission range:
10 m
- Resolution (mouse):
1000 dpi (optical)
- Frequency range:
2.4 GHz – 2.48 GHz
- Operating life of individual keys:
> 10 million operations (keyboard)
- Interface:
USB
- Current consumption:
typ. 3 mA (keyboard)
typ. 25 mA (mouse)
typ. 30 mA (receiver)
- Packaging unit:
6 desktops per master carton
12 master cartons per pallet

Order description

<i>Order number</i>	<i>Housing colour</i>	<i>Number of buttons</i>	<i>Country version</i>	<i>EAN-Code</i>
M82-24825DE	brown / black	115	Germany	4025112071058

(Other country versions upon request.)

Cherry GmbH
Cherrystraße
91275 Auerbach/Opf.
Germany

Phone: +49 9643 18-0
Internet: www.cherry.de
www.cherrycorp.com

Sales: +49 1805 243779 (01805-Cherry)
E-Mail: sales@cherry.de
Fax: +49 9643 18-1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 Cherry GmbH, Last update: 18.07.2008_V01

