

**Agilent**

## U2741A USB Modular 5.5 Digits Digital Multimeter

Data Sheet



## Features

- **Makes fast measurements with up to 100 readings per second**
- **Measures up to 300 VDC with 5.5 digits resolution**
- **Frequency and temperature measurement capability**
- **Wide voltage measurement range**
  - DC: 1  $\mu$ VDC to 300 VDC
  - AC: 1  $\mu$ Vrms to 250 Vrms
- **Wide current measurement range**
  - DC: 1  $\mu$ ADC to 2 ADC
  - AC: 1  $\mu$ Arms to 2 Arms
- **Compatibility with Hi-Speed USB 2.0, USBTMC 488.2 standards**
- **Dual-play — standalone and modular capability**
- **Bundled software — Agilent Measurement Manager (AMM)**
- **Wide range of compatible Agilent Development Environments (ADEs)**

## Introduction

The Agilent U2741A is a 5.5 digits digital multimeter (DMM), which is the latest addition to the Agilent's USB modular family. It can operate as standalone or as a modular unit when used with the U2781A USB modular instrument chassis. It comes with various features and functions to meet your needs today.




Figure 1. The U2741A DMM showing dual-play capability

### Various U2741A features to meet your demands

- Affordable and measures up to ten different measurements
- Quick and easy Hi-Speed USB 2.0 connectivity
- Dual-play capability allowing flexible configuration in simple or sophisticated test environment
- Easy-to-use bundled software to get you started with the DMM without programming
- Compatible with a wide range of ADEs to choose
- Portable, accurate, and reliable

### Value for money and feature-rich DMM

The U2741A DMM gives you an accurate 5.5 digits resolution. It offers a wide range of measurement functions and features despite its value price. The U2741A is capable of performing DC voltage, AC voltage, DC current, AC current, 2-wire resistance, 4-wire resistance, continuity, diode, frequency, and temperature measurement to meet the industrial needs.

### Quick and easy connectivity

The U2741A allows quick connection to the PC with Hi-Speed USB 2.0. The USB interface is also compliant with USBTMC 488.2 standards. You can easily connect the device using USB cable which makes the setup easy and hassle-free. This simple and easy-to-use device is ideal for design validation and educational teaching labs. Its robust design is also appropriate for manufacturing field, use in consumer electronics and semiconductor.

## Dual-play capability

The U2741A has a breakthrough design which gives the users great flexibility to use the device as a standalone or as a modular unit used in the U2781A USB modular instrument chassis. You can use this DMM as standalone for simple test configurations or slot the DMM into the chassis for more sophisticated applications systems that requires connection and triggering of other modular devices.

## Supports IVI-COM, SCPI, and compatible with wide range of ADEs

All U2741A purchases are shipped with the IVI-COM drivers. With the offered IVI-COM drivers, you are able to program the U2741A with any popular ADE that is available in the market. The U2741A is compatible with a wide range of ADEs that allows you to set up your devices in different programming environment with minimal effort as they are ready to be programmed directly using SCPI commands.

The popular development environment that is compatible with U2741A is listed below:

- Agilent VEE
- Microsoft® Visual Studio .NET
- C/C++ and Visual Basic®
- LabVIEW

## Easy-to-use bundled software

The Agilent measurement manager (AMM) bundled application software is simple and easy to use. This software offers a standard user-friendly graphical user interface (GUI) that allows you to configure and control your U2741A remotely without performing any programming task.

## Data logger function with AMM

The AMM software comes with data logger function that allows you to customize your data logging needs. Data can be stored for analysis when this option is enabled. The data capture interval range can be set from 0 s to 100 s. With this feature, you can start the U2741A to take measurement over duration and check your results when the test is completed. Data can be stored to a CSV (comma separated value) file format.





Figure 2. Example of U2741A AMM GUI

## Standard Shipped Accessory

- 12 V, 2 A AC/DC adapter
- Power cord
- Standard test lead
- USB Standard-A to Mini-B interface cable
- L-Mount kit (used with the modular instrument chassis)
- Agilent Automation-Ready CD (contains the Agilent IO Libraries Suite)
- Agilent USB Modular Products Quick Start Guide
- Agilent USB Modular Products Reference CD-ROM
- Agilent Measurement Manager Quick Reference Card
- Certificate of Calibration

## Product Outlook and Dimensions



## System Requirements

<b>Processor</b>	1.6 GHz Pentium® IV or higher
<b>Operating system</b>	Windows® XP Professional or Home Edition (Service Pack 1 or later) or Windows® 2000 Professional (Service Pack 4 or later)
<b>Browser</b>	Microsoft® Internet Explorer 5.01 or higher
<b>Available RAM</b>	512 MB or higher recommended
<b>Hard-disk space</b>	1 GB
<b>Video</b>	Super VGA 800×600
<b>Prerequisites</b>	Agilent IO Libraries Suite 14.2 or higher (version 15.0 <sup>[1]</sup> recommended), Agilent T&M Toolkit Runtime version 2.1 <sup>[2]</sup> , Agilent T&M Toolkit Redistributable Package 2.1 patch <sup>[2]</sup> , Microsoft® .NET Framework version 1.1 and 2.0 <sup>[2]</sup>

<sup>[1]</sup> Available on Agilent Automation-Ready CD.

<sup>[2]</sup> Bundled with Agilent Measurement Manager application software installer.

## General Characteristics

<b>Remote interface</b>	<ul style="list-style-type: none"> <li>• Hi-Speed USB 2.0</li> <li>• USBTMC 488.2 Class device</li> </ul>
<b>Power consumption</b>	<ul style="list-style-type: none"> <li>• +12 VDC, 2 A maximum</li> <li>• Isolated ELV power source</li> </ul>
<b>Operating environment</b>	<ul style="list-style-type: none"> <li>• One year specifications full accuracy from 18 °C to 28 °C at 50% RH</li> <li>• Altitude up to 2000 meters</li> <li>• Pollution degree 2</li> <li>• For indoor use only</li> </ul>
<b>Storage compliance</b>	<ul style="list-style-type: none"> <li>• -20 °C to +70 °C</li> <li>• Relative humidity at 5% to 90% RH (non-condensing)</li> </ul>
<b>Safety compliance</b>	Certified with: <ul style="list-style-type: none"> <li>• IEC 61010-1:2001/EN61010-1:2001 (2nd Edition)</li> <li>• Canada: CAN/CSA-C22.2 No. 61010-1-04</li> <li>• USA: ANSI/UL 61010-1:2004</li> </ul>
<b>Measurement compliance</b>	CAT II 300 V Over-voltage Protection
<b>EMC compliance</b>	<ul style="list-style-type: none"> <li>• IEC 61326-2002/EN61326:1997+A1:1998+A2:2001+A3:2003</li> <li>• Canada: ICES-001:2004</li> <li>• Australia/New Zealand: AS/NZS CISPR11:2004</li> </ul>
<b>Common mode rejection</b>	<ul style="list-style-type: none"> <li>• DC CMRR &gt;120 dB with 1k unbalanced load</li> <li>• AC CMRR &gt;70 dB at 50/60 Hz ±0.1% with 1k unbalanced load</li> </ul>
<b>Normal mode rejection ratio (NMRR)</b>	<ul style="list-style-type: none"> <li>• &gt;60 dB at 50/60 Hz ±0.1%<sup>[1]</sup></li> <li>• &gt;0 dB at 50/60 Hz ±0.1%<sup>[2]</sup></li> </ul>
<b>Shock and vibration</b>	Tested to IEC/EN 60068-2
<b>I/O connector</b>	Four banana socket terminals
<b>Dimensions (W × D × H)</b>	<ul style="list-style-type: none"> <li>• 105.00 mm x 175.00 mm x 11.50 mm (without bumpers)</li> <li>• 117.00 mm x 180.00 mm x 41.00 mm (with bumpers)</li> </ul>
<b>Weight</b>	<ul style="list-style-type: none"> <li>• 451 g (without bumpers)</li> <li>• 509 g (with bumpers)</li> </ul>
<b>Warranty</b>	One year
<b>Calibration</b>	Calibration interval of one year is highly recommended

<sup>[1]</sup> Applicable for NPLC >1.

<sup>[2]</sup> Applicable for NPLC 0.2 and 0.02.

## Product Specifications

### DC specifications<sup>[1]</sup>

Function	Range	Input impedance	Test current / Burden voltage, shunt resistance	Accuracy ±(% of reading + % of range)	Temperature Coefficient 0 °C to 18 °C 28 °C to 55 °C
<b>Voltage</b> <sup>[2]</sup>	100.000 mV	10 MΩ	–	0.015 + 0.008	0.002 + 0.0008
	1.00000 V	10 MΩ	–	0.015 + 0.005	0.001 + 0.0005
	10.0000 V	10 MΩ	–	0.018 + 0.005	0.002 + 0.0005
	100.000 V	10 MΩ	–	0.018 + 0.005	0.002 + 0.0005
	300.000 V	10 MΩ	–	0.018 + 0.005	0.002 + 0.0005
<b>Current</b> <sup>[3]</sup>	10.0000 mA	–	<0.2 V, 10 Ω	0.06 + 0.015	0.005 + 0.0025
	100.000 mA	–	<0.2 V, 1 Ω	0.06 + 0.005	0.008 + 0.002
	1.0000 A	–	<0.3 V, 0.1 Ω	0.15 + 0.007	0.005 + 0.002
	2.0000 A	–	<0.8 V, 0.1 Ω	0.15 + 0.007	0.005 + 0.002
<b>Resistance</b> <sup>[4]</sup>	100.000 Ω	–	1.0 mA	0.03 + 0.008	0.006 + 0.0008
	1.00000 kΩ	–	1.0 mA	0.03 + 0.005	0.006 + 0.0005
	10.0000 kΩ	–	100 μA	0.03 + 0.005	0.006 + 0.0005
	100.000 kΩ	–	10.0 μA	0.03 + 0.005	0.006 + 0.0005
	1.00000 MΩ	–	1 μA	0.06 + 0.005	0.01 + 0.0005
	10.0000 MΩ	–	225 nA	0.25 + 0.005	0.025 + 0.0005
	100.000 MΩ	–	225 nA // 10MΩ	2.0 + 0.005	0.3 + 0.0005
<b>Diode test</b> <sup>[5]</sup>	1.0000 V	–	1.00 mA	0.015 + 0.03	0.005 + 0.0005
<b>Continuity Test</b> <sup>[6]</sup>	1.0000 kΩ	–	1.00 mA	0.05 + 0.03	0.005 + 0.0005

<sup>[1]</sup> Specifications are based on 30 minutes warm-up time, NPLC 20 resolution, and calibration temperature within 18 °C to 28 °C. For NPLC 0 and 0.025, add 0.01% of range.

<sup>[2]</sup> 120% over range on all ranges except 300 VDC. Input protection up to 300 VDC.

<sup>[3]</sup> Input protected with externally accessible 2 A, 250 V fast blown fuse.

<sup>[4]</sup> Specifications are for 4-wire ohm or 2-wire ohms using null function in AMM software. If without null function in AMM software, add 0.2 Ω additional error. Input protection up to 300 Vdc. Specifications apply for NPLC ≥1.

<sup>[5]</sup> Specifications are for the voltage measured at the input terminals only.

<sup>[6]</sup> Continuity threshold is fixed at less than 10 Ω.

### DC current settling considerations

Switching current from >1 A to lower current measurement may cause an additional error approximately 0.3% of reading due to self- heating, and will generally dissipate within a minute.

## AC specifications<sup>[1]</sup>

### AC accuracy for voltage

Function	Range	Accuracy input $\pm$ (% of reading + % of range) Frequency (Hz)			
		20 ~ 45	45 ~ 10k	10k ~ 30k	30k ~ 100k <sup>[3]</sup>
Voltage <sup>[2]</sup>	100.000 mVrms	1 + 0.1	0.2 + 0.1	1.5 + 0.3	5.0 + 0.3
	1.00000 V	1 + 0.1	0.2 + 0.1	1.0 + 0.1	3.0 + 0.2
	10.0000 V	1 + 0.1	0.3 + 0.1	1.0 + 0.1	3.0 + 0.2
	100.000 V	1 + 0.1	0.3 + 0.1	1.0 + 0.1	3.0 + 0.2
	250.000 V <sup>[4]</sup>	1 + 0.1	0.3 + 0.1	1.0 + 0.1	3.0 + 0.2

<sup>[1]</sup> Specifications are based on 30 minutes warm-up time and calibration temperature within 18 °C to 28 °C. In manual range, the settling time is 2.6 seconds while in autorange, the first measurement accuracy is <1% .

<sup>[2]</sup> Specifications are for sine wave inputs more than 5% of range. 120% over range on all ranges except 250 VAC. Maximum crest factor of 5 at full scale. Input impedance is 1 M $\Omega$  in parallel with capacitance less than 120 pF, AC couple with up to 300 VDC.

<sup>[3]</sup> Additional error to be added as frequency more than 30 kHz and signal input less than 10% of range. 30 kHz to 100 kHz: add 0.003% of range per kHz.

<sup>[4]</sup> Input signal has to be more than 50 Vrms.

### Temperature coefficient for voltage (0 °C to 18 °C, 28 °C to 55 °C)

	Range	Frequency (Hz) (% of reading + % of range)			
		20 ~ 45	45 ~ 10k	10k ~ 30k	30k ~ 100k
Temperature coefficient	100.000 mVrms, 1.00000 V, 10.0000 V, 100.000 V, 250.000 V	0.02 + 0.02	0.02 + 0.02	0.05 + 0.02	0.1 + 0.02

### AC accuracy for current<sup>[1]</sup>

Function	Range	Burden voltage / Current shunt	Accuracy input (% of reading + % of range) Frequency (Hz)		
			20 ~ 45	45 ~ 1k	1k ~ 10k
Current <sup>[2]</sup>	10.0000 mA	<0.2 V, 10 $\Omega$	1.5 + 0.1	0.5 + 0.1	2 + 0.2
	100.000 mA	<0.2 V, 1 $\Omega$	1.5 + 0.1	0.5 + 0.1	2 + 0.2
	1.00000 A	<0.3 V, 0.1 $\Omega$	1.5 + 0.1	0.5 + 0.1	2 + 0.2
	2.0000 A	<0.8 V, 0.1 $\Omega$	1.5 + 0.1	0.5 + 0.1	2 + 0.2

<sup>[1]</sup> In manual range, the settling time is 2.6 seconds while in autorange, the first measurement accuracy is <1%.

<sup>[2]</sup> Input protected with externally accessible 2 A, 250 V fast blown fuse.

**Temperature coefficient for current (0 °C to 18 °C, 28 °C to 55 °C)**

	Range	Frequency (Hz) (% of reading + % of range)		
		20 ~ 45	45 ~ 10k	10k ~ 30k
Temperature coefficient	10.0000 mA, 100.000 mA, 1.00000 A, 2.0000 A	0.02 + 0.02	0.02 + 0.02	0.02 + 0.02

**Frequency specifications<sup>[1]</sup>**

**Frequency accuracy**

Function	Range	Accuracy (% of reading + % of range)	Minimum input frequency	Temperature coefficient (% of range)
Frequency	20 to 300 kHz	0.0200 + 0.003	1 Hz	0.005

**Frequency sensitivity for AC voltage**

Function	Input range	Minimum sensitivity (RMS sine wave) Frequency (Hz)	
		20 ~ 100 k	100 ~ 300 k
AC voltage	100 mV <sup>[2]</sup>	20 mV	20 mV
	1 V	100 mV	120 mV
	10 V	1 V	1.2 V
	100 V	10 V	20 V
	250 V	100 V	120 V

<sup>[1]</sup> Frequency measurement can only be done in auto range mode. Specifications are for 30 minutes warm-up time, using one second aperture. Measuring method is using reciprocal counting technique with AC coupled input at AC voltage function. Gate time of 0.1 second or 1 second.

<sup>[2]</sup> Only applicable for square wave measurement.

**Temperature specifications**

**Temperature accuracy**

Function	Thermistor type	Range	Accuracy	Temperature coefficient
Temperature	5 kΩ thermistor	-80.0 °C to 150 °C -112 °F to 302 °F	Probe accuracy + 0.2 °C	0.002 °C





### Agilent Email Updates

[www.agilent.com/find/emailupdates](http://www.agilent.com/find/emailupdates)

Get the latest information on the products and applications you select.



### Agilent Direct

[www.agilent.com/find/agilentdirect](http://www.agilent.com/find/agilentdirect)

Quickly choose and use your test equipment solutions with confidence.



[www.agilent.com/find/open](http://www.agilent.com/find/open)

Agilent Open simplifies the process of connecting and programming test systems to help engineers design, validate and manufacture electronic products. Agilent offers open connectivity for a broad range of system-ready instruments, open industry software, PC-standard I/O and global support, which are combined to more easily integrate test system development.

Microsoft, Windows, and Visual Studio are registered trademarks of Microsoft Corporation in the United States and/or other countries.

## Remove all doubt

Our repair and calibration services will get your equipment back to you, performing like new, when promised. You will get full value out of your Agilent equipment throughout its lifetime. Your equipment will be serviced by Agilent-trained technicians using the latest factory calibration procedures, automated repair diagnostics and genuine parts. You will always have the utmost confidence in your measurements.

Agilent offers a wide range of additional expert test and measurement services for your equipment, including initial start-up assistance, onsite education and training, as well as design, system integration, and project management.

For more information on repair and calibration services, go to:

[www.agilent.com/find/removealldoubt](http://www.agilent.com/find/removealldoubt)

[www.agilent.com](http://www.agilent.com)

[www.agilent.com/find/U2741A](http://www.agilent.com/find/U2741A)

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

### Americas

Canada	(877) 894-4414
Latin America	305 269 7500
United States	(800) 829-4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Thailand	1 800 226 008

### Europe & Middle East

Austria	01 36027 71571
Belgium	32 (0) 2 404 93 40
Denmark	45 70 13 15 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125 €/minute
Germany	07031 464 6333**
	**0.14 €/minute
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
Switzerland	0800 80 53 53
United Kingdom	44 (0) 118 9276201

Other European Countries:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

Revised: July 17, 2008

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2008  
Printed in USA, Aug 4, 2008  
5989-9361EN



Agilent Technologies