




Top View of Assembly




SECTION A-A End View of Assembly




1555K




SECTION B-B Side View of Assembly




Top View Looking Inside Box




Lid



Available 16 Gauge Steel Plate



Maximum P.C. Board Size



NOTE: Hole patterns same as seen in top view of box.

NOTE
 Purchased assembly includes box, lid and 4 cover screws.
 Cover screws should be torqued to 2.5 lbf-in (30 cN-m)
 Polycarbonate version is 508 approved
 Enclosure Type 4X, 4, 12 File# E65324

1555K	
1555K Regular Enclosure	
General Purpose ABS	1555KGY
Polycarbonate	1555K2GY
ACCESSORIES	
Heavy Duty 16 Gauge Galvanized Steel Panels	1554JPL
Steel Panel / P.C. Board Machine Screw [M3 X 8mm Nickel Plated]	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [6 X 1/4" (6.4mm) Nickel Plated]	1598ATS100
Cover Screws (Pkg 4)	SC1554
[M4 X 20mm Stainless Steel]	

