FLUKE ®

570 Series Precision Infrared Thermometers

New



Fluke 576



Included Accessories
Fluke 572: Hard case, 2 batteries
Fluke 574: Hard case, 2 batteries,
Thermocouple K probe, 220V power supply,
DataTemp software, RS232 cable
Fluke 576: Hard case, 2 batteries,
Thermocouple K probe, DataTemp software,

Ordering Information

Fluke 572
Fluke 574
Fluke 576
Fluke 574
Fluke 574
Fluke 576
Fluke 574
Fluke 575
Fluke 576
Fluke

Measure temperature with ease and precision

The Fluke 570 series are the most advanced IR non-contact thermometers, and are ideal for predictive and preventative maintenance applications.

Offering a broad temperature range and a true dimension laser sighting system for precise targeting resulting in more accurate measurements. When requiring analysis and documentation use the 100-point data logging and software for graphing and analysis. The top-of-the-range Fluke 576 even has a built-in digital camera that photographs the location when the temperature measurement is made. From close-up electrical connections, to fardistance room balancing checks, the Fluke 570 series can take IR temperature measurements with ease and precision.

- Enhanced optics allows measurements of smaller objects from farther away
- True Dimension™ three-dot laser sighting system highlights the true diameter of measurement spots at all distances
- Adjustable emissivity setting and 30 pre-set common material values for more accurate measurements
- 100 data point memory for storage of measurements (Fluke 574, 576) and photographic images (Fluke 576)
- Instantly captures photographs of temperature measurement locations for improved documentation (Fluke 576 only)

Features

	572	574	576	
Temperature range	-30 to 900°C			
Optical resolution	Standard: 60:1 Close focus: 50:1			
3 dot laser beam for accurate targeting	•	•	•	
Adjustable emissivity	•	•	•	
Bar graph display	•	•	•	
Backlit LCD display	•	•	•	
Use selectable °C or °F	•	•	•	
Audible and visible Hi/Lo Alarm	-/●	●/●	●/●	
MIN/MAX	•	•	•	
AVG/DIF readings		•	•	
Datalogging (number of measurements)		100	100	
PC interface		RS232	USB	
Built-in Digital camera			•	

Specifications

	572	574	576	
Temperature range	−30 to 900°C			
Response time	250ms (95 % of reading)			
Resolution	0.1°C of reading up to 900°C			
Repeatability	±0.5% of reading or ±1°C*			
Accuracy: (assumes ambient operating temperature of 23 °C to 25 °C)	$\pm 0.75\%$ of reading, $\pm 0.75^{\circ}$ C *			
Typical distance to target	10,5 m			
Emissivity	Digitally adjustable from 0.10 to 1.0 by 0.01			

*whichever is greater.

Battery Life:

Fluke 572, 574: 10 hours typical Fluke 576: 8 hours typical (13 hours with photographic mode off)

Size (HxWxD):

Fluke 572/574: 200 mm x 170 mm x 55 mm Fluke 576: 240 mm x 170 mm x 55 mm **Weight:** Fluke 572: 0.480 kg Fluke 574: 0.480 kg

Fluke 576: 0.580 kg

Two years warranty

Recommended Accessories





AN5

C570

USB cable.