

Type: **MFD-TP12-PT-A**

Article No.: **106042**

Sales text **E/A MFD 24VDC,Trans., 2E x PT100**



IP20, springloaded terminals


Ordering information

Description		24 V DC for MFD-CP8... (from device version 08), temperature range can be set.
Inputs		
Digital		6
of which can be used as analog		2
Upper value of setting range		2
Outputs		
Transistor	4	
Temperature range		-40...+90 °C 0...+250 °C 0...+400 °C

Notes concerning the product group

Accessories

Page



- | | |
|---|--------------------------|
| 1 Ethernet gateway | → 101520 |
| 2 Connection cable | → 280887 |
| 3 Programming software | → 266040 |
| 4 PC programming cable | → 256277 |
| 5 I/O expansion | → 212314 |
| 6 Output expansion, bus module, coupling module | → 212315 |
| 7 Display/keypad | → 265251 |
| 8 Power supply unit/CPU | → 265253 |
| 9 I/O module | → 265254 |
| 10 Memory card | → 256279 |
| 11 easy-NET | → 256283 |
| 12 Switched-mode power supply unit | → 212319 |

General

Standards			EN 61000–6–1/-2/-3/-4, IEC 60068–2–6, IEC 60068–2–27
Weight		kg	0,14
Mounting			Fitted into the power supply unit.

Terminal capacities

Solid		mm ²	0.24 (AWG 24 – 12)
Flexible with ferrule		mm ²	0.22.5 (AWG 24 – 12)
Standard screwdriver		mm	3.5 × 0.6

Climatic environmental conditions

Operating ambient temperature		°C	–25 to 55, cold as per IEC 60068–2–1, heat as per IEC 60068–2–2
Condensation			Take appropriate measures to prevent condensation
Storage		°C	... 40...+70
Relative humidity, non-condensing (IEC/EN 60068–2–30)		%	5...95
Air pressure (operation)		hPa	795...1080

Ambient conditions, mechanical

Pollution degree			2
Degree of protection IEC/EN 60529			IP 20

Vibrations (IEC/EN 60068–2–6)			
Constant amplitude 0.15 mm		Hz	10...57
Constant acceleration 2 g		Hz	57...150
Mechanical shock resistance (IEC/EN 60068–2–27) semi–sinusoidal 15 g/11 ms		Impacts	18
Drop to IEC/EN 60068–2–31	Drop height	mm	50
Free fall, packaged (IEC/EN 60068–2–32)		m	1
Mounting position			horizontal, vertical
Electromagnetic compatibility (EMC)			
Electrostatic discharge (IEC/EN 61000–4–2, Level 3, ESD)			
Air discharge		kV	8
Contact discharge		kV	6
Electromagnetic fields (IEC/EN 61000–4–3, RFI)		V/m	10
Radio interference suppression (EN 55011)			EN 55011 Class B, EN 55022 Class B
Burst pulses (IEC/EN 61000–4–4, level 3)			
Supply cables		kV	2
Signal lines		kV	2
High–energy pulses (surge) (IEC/EN 61000–4–5)		kV	2 (supply cables, symmetrical)
High–energy pulses (surge) (IEC/EN 61000–4–5, level 2)		kV	0.5 (supply cables, symmetrical)
Immunity to line–conducted interference to (IEC/EN 61000–4–6)		V	10
Insulation resistance			
Clearance in air and creepage distances			EN 50178, UL 508, CSA C22.2, no. 142
Insulation resistance			EN 50178
Digital inputs 24 V DC			
Number			6
Inputs can be used as analog inputs			2 (I11, I12)
Potential isolation			
From power supply			No
Between digital inputs			No
From the outputs			Yes
for Program code			Yes


Rated operational voltage	U_e	V DC	24
On 0 signal	U_e	V DC	$< 5.0 \text{ (I1 - I4)} < 8.0 \text{ (I11, I12)}$
On 1 signal	U_e	V DC	$> 15.0 \text{ (I1 - I4)} > 8.0 \text{ (I11, I12)}$
Input current on 1 signal			
I11, I12		mA	2.2 (at 24 V DC)
Delay time from 0 to 1			
Debounce ON		ms	20
Debounce OFF		ms	Normally 0.1 (I1 – I4), Normally 0.25 (I11 – I12)
Delay time from 1 to 0			
Debounce ON		ms	20
Debounce OFF		ms	Normally 0.1 (I1 – I4), normally 0.2 (I11, I12)
Cable length (unscreened)		m	100
Frequency counter			
Quantity			4 (I1, I2, I3, I4)
Counter frequency		kHz	< 3
Pulse shape			Square
Incremental counter			
Quantity			2 (I1 + I2, I3 + I4)
Counter frequency		kHz	3
Pulse shape			Square
Signal offset			90°
Rapid counter inputs			
Number			4 (I1, I2, I3, I4)
Counter frequency		kHz	< 3
Pulse shape			Square
Cable length, screened		m	< 20

Analog inputs

Potential isolation			
From power supply			No
From the digital inputs			No
From the outputs			Yes
for Program code			Yes
Input type			DC voltage
Signal range	V DC		0 – 10
Resolution, analog	V		0,01
Resolution, digital	V		0,01
Resolution	Bit		10 (value 0 – 1023)

Input impedance	k	11,2
Accuracy of actual value		
two MFD devices	%	± 3
Within a single device	%	± 2
Conversion time, analog/digital	ms	Each CPU cycle
Input current	mA	< 1
Cable length screened	m	< 30

Dimensions



Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn
 E-Mail: catalog@moeller.net, Internet: www.moeller.net, http://catalog.moeller.net
 Copyright 2006 by Moeller GmbH. HPL-C2007G V2.1