


REV	REVISIONS	DRN	APP	DATE
A	NEW RELEASE	MC	HG	8-20-96
B	REVISED LED SPECS UPDATED TO CREO FORMAT	LD	NO	6-28-19



LED CHARACTERISTICS	LED COLOR	MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	RED	3.7	12.6		mcd	$I_F = 20\text{mA}$
	GREEN	1.1	3.7			
FORWARD VOLTAGE	RED		1.8	2.4	V	$I_F = 20\text{mA}$
	GREEN		2.1	2.6		
DOMINANT WAVELENGTH	RED		638		nm	
	GREEN		569			
PEAK WAVELENGTH	RED		660		nm	
	GREEN		565			
2 X 1/2 INTENSITY ANGLE	RED		200		deg	
	GREEN					
REVERSE CURRENT	RED		100		uA	$V_R = 5\text{V}$
	GREEN					
CAPACITANCE	RED		30		pF	$V_F = 0$ $f = 1\text{MHz}$
	GREEN		35			

ABSOLUTE MAXIMUM RATINGS AT 25° C AMBIENT	RED	GREEN	UNITS
POWER DISSIPATION	100		mW
DERATE LINEARLY FROM 50° C	.5	.4	mA/C
CONTINUOUS FORWARD CURRENT	40	30	mA
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 01 ms PULSE WIDTH)	200	120	mA
LEAD SOLDERING TEMPERATURE, 5 SEC., 1/16mm (.063") FROM BODY	260		°C
OPERATING TEMPERATURE	-55 to +100		°C
STORAGE TEMPERATURE	-55 to +100		°C

NOTES:

- DIALIGHT P/N 521-9628F
- EPOXY COLOR: WHITE DIFFUSED
- DIE: AlGaAs RED/Gap GREEN.
- THIS PART IS RoHS COMPLIANT. EACH BAG IS MARKED WITH RoHS COMPLIANT MARKINGS



ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.		
DIALIGHT CORP INTERNAL REFERENCE ONLY = 3D MODEL : 5219628-B.2		
SCALE: 8.000	DRAWING NUMBER	REV
ALL DIM's: INCH (mm)	C-16126	B
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE RED/GREEN BICOLOR LED	
FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005 DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	MATERIAL	
FINISH		
FSCM 83330	SHEET 1 OF 1	FAMILY TABLE:
<small>1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727 (732) 919-3119 www.dialight.com</small>		