


	REVISIONS							
REV	ECO	DESCRIPTION	DATE	BY	APPR			
A1	-	RELEASE NEW DRAWING	18MAY20	IAN	TOMMY			
A2	-	MODIFY PRODUCT NAME	11AUG20	IAN	TOMMY			







NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

 $\hbox{HOUSING: THERMOPLASTIC; BLACK}$

SEAL: SILICONE RUBBER

2. MODIFICATIONS: SMOOTH RING ADAPTER (SRA);

REDUCED DIA. WIRE SEAL;

3. SPECIFICATIONS:


3.1 OPERATING TEMPERATURE: -55°C TO +125°C.

3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.

- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION).
- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP04-24-18P* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
8	3.43 mm (.135 in)	5.59 mm (.220 in)	8-10 AWG (10.0-5.0mm²)	60 AMPS
12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS
16	1.35 mm (.053 in)	3.05 mm (.120 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS



	AHDP06-24-18SR-SRA		-SRA	RE	:HDP26-24-18SE		
	PART N	IUMBEF	₹		DESCRIPTION [
QUANTITY			MAT	ERI	ALS LIST		
UNLESS OTHER		SIGI	VATURES	DATE	Amphonol		
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		DRAWN:	IAN.XIAO	11AUG20	Amphenol		
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	ORION.LI	12AUG20	Sine Systems - www.amphenol-sine.com		
3) Note reference	- 🖈	ENGINEER:			44724 Morley Drive		
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMYXIE	13AUG20	Clinton Township, MI 48036		
		CUSTOMER:			PLUG, SIZE 24, 18-SOCKET,		
			IG IS SUPPLIED F		RD01 SEAL,SRA,DURAMATE AHDP SERIE	S	
PROCESS SPECIFICATIONS: SPECIF SHOWN THE AM OF REF		SPECIFICATI SHOWN HER THE AMPHEN OF REPRODU	ONS AND PERFORE EON ARE THE PR IOL CORPORATIO JCTION ARE IMPL ARE SUBJECT TO	RMANCE DATA OPERTY OF IN. NO RIGHTS IED. ALL	B C- AHDP06-24-18SR-SRA	A2	
NEXT ASS'Y:			RING VARIATIONS	S.	SCALE: NONE DURAMATE SHEET 1 OF	1	

AT Series™ - Contact Size 16 Options

Machined Contacts, Sockets & Pins					
Part Number	Description		AWG	Туре	
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined	
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined	
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined	
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined	
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined	
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined	
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined	
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined	
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined	
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined	
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined	
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined	

Tooling - Machined Contacts					
Part	Part Number	Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

	Contact Removal Tools					
Part	Part Number	Description				
3	ATRT-100	Used for removal of contacts for A Series™ products				
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16				
	A114017	Sealing Plug, Size 16, White				

	Stamped & Formed Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Type		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		

	Tooling - Stamped & Formed Contacts					
Part	Part Number	Description				
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)				
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)				
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)				
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)				
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)				
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)				
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)				

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021

MagnaMate™ ATHP - DuraMate™ AHDP - DuraMate™ AHDM Series - Contact Size 12 Options

Machined Contacts, Sockets & Pins						
Part Number	Size	AWG	Type			
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined		
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined		
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined		
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined		
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined		
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined		

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective					
Part Number Description Size AWG Tyl			Туре		
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined	
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined	

Tooling - Machined Contacts			
Part	Part Number	Description	
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)	
33	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)	

Contact Removal Tools				
Part	Part Number	Description		
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12		
	A114017	Sealing Plug, Size 12, White		

Stamped & Formed Contacts, Sockets & Pins					
Part Number	Description		AWG	Туре	
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed	
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed	
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed	
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed	
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed	
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed	
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed	
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed	

Tooling - Stamped & Formed Contacts				
Part	Part Number	Description		
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)		
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series		
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)		
	ATT-12-01	Hand Crimp Tool - Size 12, 10AWG (S&F contacts only)		

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 01/2022

DuraMate™ ATHD Series™ - Contact Size 8 Options

Machined Contacts, Pins and Sockets					
Part Number	Description	Size	AWG	Туре	Amps
AT60-204-08141	Male Contact - Pin, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A
AT62-203-08141	Female Contact - Socket, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A

Tooling - Machined Contacts				
Part	Part Number	Description		
	WA23	Heavy Duty Pneumatic Crimp Tool -Uses Universal Positioner Part No. WA23-101DA and Crimp Locator MFX-3961		
	WA23-2	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 8		
Variety by Barrier B	WA23-10	Contact Locator, Size 8		
NAM	96-978-22	Crimper and Dies -for Size 10mm²-185mm² Wires		

Contact Removal Tools				
Part	Part Number	Description		
	AT114008	Contact Removal Tool, Plastic, Size 8, 8-10AWG		